

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250521

Luminaire Tested: **LD8B100D010 ER8B100950 8LBM0GPH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250521  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P14005)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B100D010 ER8B100950 8LBM0GPH  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT  
90 CRI 5000 CCT WITH GRAPHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8777.0 lumens  
Efficiency: N/A  
Efficacy: 82.6 lumens/watt  
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 106.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250521

CATALOG NUMBER: LD8B100D010 ER8B100950 8LBM0GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P250521

CATALOG NUMBER: LD8B100D010 ER8B100950 8LBM0GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	108	106	111	109	107	105	105	103	101	101	100	98	98	96	95	94
2	108	103	99	96	106	102	98	95	98	95	93	95	93	91	93	91	89	87
3	103	96	92	88	101	95	91	87	92	89	86	90	87	84	88	85	83	81
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76
5	93	85	79	75	91	84	78	74	82	77	74	80	76	73	79	75	72	71
6	88	79	73	69	87	79	73	69	77	72	69	76	71	68	74	71	68	66
7	84	75	69	65	82	74	68	64	73	68	64	72	67	64	70	66	63	62
8	80	70	64	60	79	70	64	60	69	64	60	68	63	60	67	63	59	58
9	76	66	61	57	75	66	60	57	65	60	56	64	59	56	63	59	56	55
10	72	63	57	53	71	62	57	53	62	57	53	61	56	53	60	56	53	51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	343254
5°	334577
10°	299932
15°	267131
20°	243690
25°	221408
30°	181551
35°	119483
40°	59604
45°	22184
50°	6740
55°	812
60°	469
65°	0
70°	343
75°	1358
80°	0
85°	1344



TEST NUMBER: P250521

CATALOG NUMBER: LD8B100D010 ER8B100950 8LBM0GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	991.0	11.3
10°-20°	2356.3	26.8
20°-30°	2935.5	33.4
30°-40°	1980.1	22.6
40°-50°	468.2	5.3
50°-60°	34.2	0.4
60°-70°	6.1	0.1
70°-80°	4.5	0.1
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6282.8	71.6
0°-40°	8262.9	94.1
0°-60°	8765.3	99.9
0°-90°	8777.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8777.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	11132	
5°	10809	991
15°	8368	2356
25°	6507	2936
35°	3174	1980
45°	509	468
55°	15	34
65°	0	6
75°	11	5
85°	4	1
90°	0	



TEST NUMBER: P250521

CATALOG NUMBER: LD8B100D010 ER8B100950 8LBM0GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	11131.5
2.5°	11112.6
5°	10808.8
7.5°	10258.3
10°	9578.8
12.5°	8937.1
15°	8367.7
17.5°	7877.9
20°	7426.1
22.5°	6993.3
25°	6507.4
27.5°	5873.3
30°	5098.8
32.5°	4161.1
35°	3174.0
37.5°	2270.4
40°	1480.7
42.5°	884.6
45°	508.7
47.5°	284.7
50°	140.5
52.5°	64.6
55°	15.1
57.5°	3.8
60°	7.6
62.5°	11.4
65°	0.0
67.5°	7.6
70°	3.8
72.5°	3.8
75°	11.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	3.8
87.5°	0.0
90°	0.0

(END OF REPORT)