

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243888

Luminaire Tested: **LD8B10D010 ER8B10840 8LBNOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P243888
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-10)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B10840 8LBN0LI
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 4000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1101.0 lumens
Efficiency: N/A
Efficacy: 107.9 lumens/watt
Spacing Criteria (0/90/45): 0.25 / 0.25 / 0.32
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P243888

CATALOG NUMBER: LD8B10D010 ER8B10840 8LBN0LI

Luminous Intensity Polar Plot





TEST NUMBER: P243888

CATALOG NUMBER: LD8B10D010 ER8B10840 8LBN0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	102	100	108	104	101	99	101	99	96		98	96	94		95	94	92	91
3	106	100	96	93	104	99	95	92	96	93	91		94	92	89		92	90	88	87
4	102	95	91	87	100	94	90	87	92	89	86		90	87	85		89	86	84	83
5	98	91	86	83	96	90	86	82	88	85	82		87	84	81		85	83	80	79
6	94	87	82	79	93	86	82	78	85	81	78		83	80	77		82	79	77	76
7	91	83	78	75	90	83	78	75	81	77	74		80	77	74		79	76	74	72
8	88	80	75	72	86	79	75	71	78	74	71		77	74	71		76	73	71	70
9	85	77	72	69	84	76	72	69	75	71	68		75	71	68		74	70	68	67
10	82	74	69	66	81	73	69	66	73	69	66		72	68	66		71	68	65	64

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	166337
5°	115530
10°	60795
15°	38465
20°	28585
25°	22473
30°	16180
35°	6942
40°	2419
45°	929
50°	216
55°	81
60°	0
65°	109
70°	36
75°	83
80°	124
85°	0



TEST NUMBER: P243888

CATALOG NUMBER: LD8B10D010 ER8B10840 8LBN0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	299.2	27.2
10°-20°	347.7	31.6
20°-30°	300.0	27.3
30°-40°	130.2	11.8
40°-50°	20.4	1.9
50°-60°	1.5	0.1
60°-70°	0.8	0.1
70°-80°	0.8	0.1
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	946.9	86.0
0°-40°	1077.1	97.8
0°-60°	1099.0	99.8
0°-90°	1101.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1101.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5394	
5°	3732	299
15°	1205	348
25°	660	300
35°	184	130
45°	21	20
55°	2	1
65°	2	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P243888

CATALOG NUMBER: LD8B10D010 ER8B10840 8LBN0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	5394.2
2.5°	4871.1
5°	3732.3
7.5°	2661.8
10°	1941.6
12.5°	1489.8
15°	1204.9
17.5°	1013.3
20°	871.1
22.5°	749.7
25°	660.5
27.5°	566.4
30°	454.4
32.5°	315.9
35°	184.4
37.5°	103.1
40°	60.1
42.5°	37.3
45°	21.3
47.5°	17.2
50°	4.5
52.5°	2.2
55°	1.5
57.5°	0.7
60°	0.0
62.5°	0.4
65°	1.5
67.5°	1.1
70°	0.4
72.5°	1.9
75°	0.7
77.5°	0.0
80°	0.7
82.5°	0.4
85°	0.0
87.5°	0.7
90°	0.0

(END OF REPORT)