

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244464

Luminaire Tested: **LD8B10D010 ER8B10840 8LBS0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244464
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-13)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B10840 8LBS0H
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 4000 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1227.0 lumens
Efficiency: N/A
Efficacy: 120.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.23
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244464

CATALOG NUMBER: LD8B10D010 ER8B10840 8LBS0H

Luminous Intensity Polar Plot





TEST NUMBER: P244464

CATALOG NUMBER: LD8B10D010 ER8B10840 8LBSOH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	85	83	81
3	98	90	84	79	96	89	83	78	86	81	77		83	79	76		81	78	75	73
4	91	82	75	70	89	81	75	70	79	73	69		76	72	68		74	70	67	65
5	85	75	68	63	83	74	67	62	72	66	62		70	65	61		69	64	60	59
6	80	69	61	56	78	68	61	56	66	60	56		65	59	55		63	58	55	53
7	75	63	56	51	73	63	56	51	61	55	50		60	54	50		59	54	50	48
8	70	58	51	46	68	58	51	46	57	50	46		55	50	46		54	49	45	44
9	66	54	47	42	64	53	47	42	52	46	42		51	46	42		51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	38		48	42	38		47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	21959
5°	21885
10°	21718
15°	21565
20°	21419
25°	21136
30°	20485
35°	19327
40°	17567
45°	14452
50°	9633
55°	5016
60°	2368
65°	1240
70°	622
75°	429
80°	320
85°	248



TEST NUMBER: P244464

CATALOG NUMBER: LD8B10D010 ER8B10840 8LBSOH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.1	5.5
10°-20°	190.7	15.5
20°-30°	285.2	23.2
30°-40°	319.0	26.0
40°-50°	250.3	20.4
50°-60°	91.3	7.4
60°-70°	18.6	1.5
70°-80°	4.0	0.3
80°-90°	0.8	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	542.9	44.2
0°-40°	862.0	70.2
0°-60°	1203.5	98.1
0°-90°	1227.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1227.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	712	
5°	707	67
15°	676	191
25°	621	285
35°	513	319
45°	331	250
55°	93	91
65°	17	19
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P244464

CATALOG NUMBER: LD8B10D010 ER8B10840 8LBSOH

CANDELA DISTRIBUTION (FULL):

	0°
0°	712.1
2.5°	711.0
5°	707.0
7.5°	701.2
10°	693.6
12.5°	684.9
15°	675.5
17.5°	665.0
20°	652.7
22.5°	638.3
25°	621.2
27.5°	600.3
30°	575.3
32.5°	546.0
35°	513.4
37.5°	476.9
40°	436.4
42.5°	388.2
45°	331.4
47.5°	267.4
50°	200.8
52.5°	140.7
55°	93.3
57.5°	59.7
60°	38.4
62.5°	25.3
65°	17.0
67.5°	10.9
70°	6.9
72.5°	4.7
75°	3.6
77.5°	2.5
80°	1.8
82.5°	1.1
85°	0.7
87.5°	0.4
90°	0.0

(END OF REPORT)