

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246264

Luminaire Tested: **LD8B10D010 ER8B10840 8LBW0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246264
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-47)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B10840 8LBW0B
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 4000 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 728.0 lumens
Efficiency: N/A
Efficacy: 71.4 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.08 / 1.02
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246264

CATALOG NUMBER: LD8B10D010 ER8B10840 8LBW0B

Luminous Intensity Polar Plot





TEST NUMBER: P246264

CATALOG NUMBER: LD8B10D010 ER8B10840 8LBW0B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	106	111	108	106	104	104	102	101		101	99	98		97	96	95	93
2	107	102	98	95	105	101	97	94	97	94	92		94	92	90		92	90	88	86
3	102	95	90	86	100	94	89	85	91	87	84		89	85	82		86	84	81	80
4	96	88	83	78	94	87	82	78	85	80	77		83	79	76		81	78	75	74
5	91	82	76	72	89	81	76	71	80	75	71		78	74	70		76	73	70	68
6	86	77	71	66	85	76	70	66	74	69	65		73	68	65		72	68	65	63
7	82	72	66	61	80	71	65	61	70	64	61		69	64	60		67	63	60	58
8	77	67	61	57	76	67	61	57	66	60	56		65	60	56		64	59	56	54
9	73	63	57	53	72	63	57	53	62	56	52		61	56	52		60	55	52	51
10	70	59	53	49	68	59	53	49	58	53	49		57	52	49		57	52	49	47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	20528
5°	20012
10°	19479
15°	19116
20°	18619
25°	17958
30°	16479
35°	12633
40°	6010
45°	2289
50°	1118
55°	457
60°	111
65°	29
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P246264

CATALOG NUMBER: LD8B10D010 ER8B10840 8LBW0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.9	8.4
10°-20°	168.5	23.1
20°-30°	240.6	33.1
30°-40°	199.4	27.4
40°-50°	49.2	6.8
50°-60°	8.9	1.2
60°-70°	0.5	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	470.1	64.6
0°-40°	669.5	92.0
0°-60°	727.5	99.9
0°-90°	728.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	728.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	666	
5°	646	61
15°	599	169
25°	528	241
35°	336	199
45°	52	49
55°	8	9
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P246264

CATALOG NUMBER: LD8B10D010 ER8B10840 8LBW0B

CANDELA DISTRIBUTION (FULL):

	0°
0°	665.7
2.5°	660.2
5°	646.5
7.5°	633.2
10°	622.1
12.5°	611.4
15°	598.8
17.5°	584.0
20°	567.4
22.5°	548.5
25°	527.8
27.5°	499.8
30°	462.8
32.5°	410.7
35°	335.6
37.5°	242.5
40°	149.3
42.5°	86.9
45°	52.5
47.5°	34.7
50°	23.3
52.5°	15.2
55°	8.5
57.5°	4.1
60°	1.8
62.5°	0.7
65°	0.4
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)