

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243816

Luminaire Tested: **LD8B10D010 ER8B10840 8LBWOLI**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P243816  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27941)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B10D010 ER8B10840 8LBW0LI  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 4000 CCT WITH SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1193.0 lumens  
Efficiency: N/A  
Efficacy: 117.0 lumens/watt  
Spacing Criteria (0/90/45): 1.34 / 1.34 / 1.17  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P243816

CATALOG NUMBER: LD8B10D010 ER8B10840 8LBW0LI

### Luminous Intensity Polar Plot





TEST NUMBER: P243816

CATALOG NUMBER: LD8B10D010 ER8B10840 8LBW0LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54
8	74	63	56	52	72	62	56	52	61	55	51	60	55	51	59	54	51	49
9	70	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	21166
5°	21792
10°	23609
15°	25830
20°	26872
25°	26774
30°	25113
35°	21058
40°	14665
45°	8399
50°	4509
55°	1860
60°	463
65°	117
70°	63
75°	36
80°	53
85°	0



TEST NUMBER: P243816

CATALOG NUMBER: LD8B10D010 ER8B10840 8LBW0LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	68.8	5.8
10°-20°	228.0	19.1
20°-30°	358.8	30.1
30°-40°	341.3	28.6
40°-50°	157.4	13.2
50°-60°	35.8	3.0
60°-70°	2.3	0.2
70°-80°	0.5	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	655.7	55.0
0°-40°	997.0	83.6
0°-60°	1190.1	99.8
0°-90°	1193.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1193.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	686	
5°	704	69
15°	809	228
25°	787	359
35°	559	341
45°	193	157
55°	35	36
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P243816

CATALOG NUMBER: LD8B10D010 ER8B10840 8LBW0LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	686.4
1°	686.1
2°	687.4
3°	691.3
4°	697.2
5°	704.0
6°	712.5
7°	721.7
8°	731.1
9°	742.2
10°	754.0
11°	765.7
12°	778.1
13°	789.9
14°	800.7
15°	809.1
16°	815.3
17°	819.6
18°	821.5
19°	821.2
20°	818.9
21°	815.0
22°	810.1
23°	803.6
24°	796.1
25°	786.9
26°	776.2
27°	762.5
28°	746.1
29°	727.2
30°	705.3
32.5°	639.7
35°	559.4
37.5°	466.1
40°	364.3
42.5°	269.3
45°	192.6
47.5°	136.4
50°	94.0
52.5°	60.1
55°	34.6
57.5°	17.3
60°	7.5
62.5°	2.9
65°	1.6



TEST NUMBER: P243816

CATALOG NUMBER: LD8B10D010 ER8B10840 8LBW0LI

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	1.0
70°	0.7
72.5°	0.7
75°	0.3
77.5°	0.3
80°	0.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)