

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246630

Luminaire Tested: **LD8B10D010 ER8B10850 8LBN0MW**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P246630  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201839)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B10D010 ER8B10850 8LBN0MW  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 5000 CCT WITH MATTE WHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1080.0 lumens  
Efficiency: N/A  
Efficacy: 105.9 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.85  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P246630

CATALOG NUMBER: LD8B10D010 ER8B10850 8LBN0MW

### Luminous Intensity Polar Plot





TEST NUMBER: P246630

CATALOG NUMBER: LD8B10D010 ER8B10850 8LBN0MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	109	106	104	101	102	100	98	98	97	95	95	94	92	90
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	83	82
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74
4	93	84	77	72	91	83	76	72	80	75	71	78	74	70	76	72	69	67
5	87	78	71	66	85	77	70	65	75	69	65	73	68	64	71	67	64	62
6	82	72	65	60	81	71	65	60	70	64	60	68	63	59	67	62	59	57
7	78	67	60	56	76	67	60	55	65	59	55	64	59	55	63	58	54	53
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49
9	70	59	53	48	69	59	52	48	58	52	48	57	51	48	56	51	47	46
10	66	56	49	45	65	55	49	45	54	49	45	54	48	45	53	48	45	43

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	34925
5°	34675
10°	31597
15°	27084
20°	24004
25°	21418
30°	17298
35°	12001
40°	7616
45°	5656
50°	4826
55°	4231
60°	3787
65°	3386
70°	2912
75°	2681
80°	2504
85°	2194



TEST NUMBER: P246630

CATALOG NUMBER: LD8B10D010 ER8B10850 8LBN0MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	103.3	9.6
10°-20°	239.0	22.1
20°-30°	284.2	26.3
30°-40°	200.9	18.6
40°-50°	103.7	9.6
50°-60°	71.1	6.6
60°-70°	46.1	4.3
70°-80°	24.2	2.2
80°-90°	7.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	626.5	58.0
0°-40°	827.4	76.6
0°-60°	1002.2	92.8
0°-90°	1080.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1080.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1133	
5°	1120	103
15°	848	239
25°	630	284
35°	319	201
45°	130	104
55°	79	71
65°	46	46
75°	22	24
85°	6	7
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P246630

CATALOG NUMBER: LD8B10D010 ER8B10850 8LBN0MW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1132.6
2.5°	1132.6
5°	1120.2
7.5°	1079.0
10°	1009.1
12.5°	925.8
15°	848.4
17.5°	784.7
20°	731.5
22.5°	681.1
25°	629.5
27.5°	564.8
30°	485.8
32.5°	400.8
35°	318.8
37.5°	245.6
40°	189.2
42.5°	152.2
45°	129.7
47.5°	113.4
50°	100.6
52.5°	89.5
55°	78.7
57.5°	69.3
60°	61.4
62.5°	53.2
65°	46.4
67.5°	40.2
70°	32.3
72.5°	27.8
75°	22.5
77.5°	18.3
80°	14.1
82.5°	10.5
85°	6.2
87.5°	3.6
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P246630

CATALOG NUMBER: LD8B10D010 ER8B10850 8LBN0MW

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)