

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250367

Luminaire Tested: **LD8B100D010 ER8B1009730 8LBN0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250367
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13948)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B100D010 ER8B1009730 8LBN0GPH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6495.0 lumens
Efficiency: N/A
Efficacy: 61.1 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 106.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250367

CATALOG NUMBER: LD8B100D010 ER8B1009730 8LBN0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P250367

CATALOG NUMBER: LD8B100D010 ER8B1009730 8LBN0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88	92	89	86	89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72	79	75	71	77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66
8	83	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P250367

CATALOG NUMBER: LD8B100D010 ER8B1009730 8LBN0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	931.7	14.3
10°-20°	2024.9	31.2
20°-30°	2173.9	33.5
30°-40°	1174.9	18.1
40°-50°	183.3	2.8
50°-60°	5.0	0.1
60°-70°	1.2	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5130.5	79.0
0°-40°	6305.4	97.1
0°-60°	6493.8	100.0
0°-90°	6495.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6495.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10378	
5°	10174	932
15°	7230	2025
25°	4819	2174
35°	1846	1175
45°	169	183
55°	0	5
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P250367

CATALOG NUMBER: LD8B100D010 ER8B1009730 8LBN0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	10378.4
1°	10398.1
2°	10388.3
3°	10352.7
4°	10284.4
5°	10173.7
6°	10021.3
7°	9816.3
8°	9559.6
9°	9264.2
10°	8935.8
11°	8591.2
12°	8233.8
13°	7876.7
14°	7545.0
15°	7229.9
16°	6940.6
17°	6661.2
18°	6401.2
19°	6157.8
20°	5923.6
21°	5696.1
22°	5481.5
23°	5267.4
24°	5043.2
25°	4818.8
26°	4591.2
27°	4331.4
28°	4045.3
29°	3753.3
30°	3447.7
31°	3119.5
32°	2791.1
33°	2466.2
34°	2138.1
35°	1845.5
37.5°	1179.5
40°	682.4
42.5°	364.0
45°	169.1
47.5°	91.2
50°	29.5
52.5°	3.3
55°	0.0
57.5°	3.3



TEST NUMBER: P250367

CATALOG NUMBER: LD8B100D010 ER8B1009730 8LBN0GPH

CANDELA DISTRIBUTION (continued):

	0°
60°	3.3
62.5°	0.0
65°	0.0
67.5°	3.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)