

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250031

Luminaire Tested: **LD8B100D010 ER8B1009730 8LBN0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250031
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13951)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B100D010 ER8B1009730 8LBN0WMH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7059.1 lumens
Efficiency: N/A
Efficacy: 66.4 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.79
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 106.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250031

CATALOG NUMBER: LD8B100D010 ER8B1009730 8LBN0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P250031

CATALOG NUMBER: LD8B100D010 ER8B1009730 8LBN0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	97	106	102	99	96	99	96	93	96	94	91	93	91	90	88
3	103	97	92	89	101	96	91	88	93	89	86	91	88	85	89	86	84	82
4	98	91	86	82	97	90	85	81	88	84	80	86	82	79	84	81	79	77
5	94	86	80	76	92	85	80	76	83	78	75	81	77	74	80	76	74	72
6	89	81	75	71	88	80	75	71	79	74	70	77	73	70	76	72	69	68
7	85	76	71	67	84	76	70	66	74	70	66	73	69	66	72	68	65	64
8	81	72	66	63	80	72	66	62	71	66	62	70	65	62	69	65	62	60
9	78	68	63	59	77	68	63	59	67	62	59	66	62	58	65	61	58	57
10	74	65	59	56	73	65	59	56	64	59	56	63	59	55	62	58	55	54

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P250031

CATALOG NUMBER: LD8B100D010 ER8B1009730 8LBN0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	933.2	13.2
10°-20°	2141.1	30.3
20°-30°	2274.6	32.2
30°-40°	1297.8	18.4
40°-50°	321.8	4.6
50°-60°	63.3	0.9
60°-70°	19.1	0.3
70°-80°	4.5	0.1
80°-90°	3.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5348.9	75.8
0°-40°	6646.6	94.2
0°-60°	7031.7	99.6
0°-90°	7059.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7059.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10282	
5°	10100	933
15°	7692	2141
25°	5022	2275
35°	2029	1298
45°	364	322
55°	59	63
65°	15	19
75°	0	5
85°	5	4
90°	0	



TEST NUMBER: P250031

CATALOG NUMBER: LD8B100D010 ER8B1009730 8LBN0WMH

CANDELA DISTRIBUTION (FULL):

0°	
0°	10281.6
1°	10301.3
2°	10293.9
3°	10257.1
4°	10193.2
5°	10099.8
6°	9977.0
7°	9807.5
8°	9613.3
9°	9385.0
10°	9134.3
11°	8869.0
12°	8584.0
13°	8294.1
14°	7996.8
15°	7692.2
16°	7404.7
17°	7114.9
18°	6842.1
19°	6564.6
20°	6301.7
22.5°	5650.6
25°	5021.6
27.5°	4346.1
30°	3599.2
32.5°	2798.2
35°	2029.3
37.5°	1397.9
40°	904.1
42.5°	572.5
45°	363.6
47.5°	238.4
50°	149.9
52.5°	91.0
55°	58.9
57.5°	46.7
60°	29.5
62.5°	27.0
65°	14.8
67.5°	14.8
70°	12.3
72.5°	7.4
75°	0.0
77.5°	2.5
80°	2.5



TEST NUMBER: P250031

CATALOG NUMBER: LD8B100D010 ER8B1009730 8LBN0WMH

CANDELA DISTRIBUTION (continued):

	0°
82.5°	4.9
85°	4.9
87.5°	2.5
90°	0.0

(END OF REPORT)