

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246953

Luminaire Tested: **LD8B120D010 ER8B120827 8LBMOLI**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P246953  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-81)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B120D010 ER8B120827 8LBM0LI  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 2700 CCT WITH SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 11888.0 lumens  
Efficiency: N/A  
Efficacy: 100.5 lumens/watt  
Spacing Criteria (0/90/45): 0.67 / 0.67 / 0.75  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 118.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P246953

CATALOG NUMBER: LD8B120D010 ER8B120827 8LBM0LI

### Luminous Intensity Polar Plot





TEST NUMBER: P246953

CATALOG NUMBER: LD8B120D010 ER8B120827 8LBM0LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94	96	94	92	94	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83
4	99	92	87	83	97	91	86	82	89	85	81	87	83	80	85	82	79	78
5	94	87	81	77	93	86	81	77	84	79	76	82	78	75	81	77	75	73
6	90	82	76	72	89	81	76	72	79	75	71	78	74	71	77	73	70	69
7	86	77	72	68	85	77	71	68	75	71	67	74	70	67	73	69	67	65
8	82	73	68	64	81	73	67	64	72	67	63	71	66	63	70	66	63	62
9	79	70	64	60	78	69	64	60	68	63	60	67	63	60	67	63	60	58
10	75	66	61	57	74	66	61	57	65	60	57	64	60	57	64	60	57	55

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	601573
5°	576492
10°	508338
15°	428402
20°	351744
25°	285095
30°	211059
35°	127045
40°	56577
45°	21996
50°	7892
55°	2301
60°	1622
65°	1211
70°	126
75°	655
80°	0
85°	1946



TEST NUMBER: P246953

CATALOG NUMBER: LD8B120D010 ER8B120827 8LBM0LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1700.3	14.3
10°-20°	3727.3	31.4
20°-30°	3801.2	32.0
30°-40°	2129.0	17.9
40°-50°	454.0	3.8
50°-60°	56.2	0.5
60°-70°	14.7	0.1
70°-80°	3.5	0.0
80°-90°	1.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	9228.8	77.6
0°-40°	11357.7	95.5
0°-60°	11868.0	99.8
0°-90°	11888.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	11888.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	19509	
5°	18624	###
15°	13419	3727
25°	8379	3801
35°	3375	2129
45°	504	454
55°	43	56
65°	17	15
75°	6	3
85°	6	2
90°	0	



TEST NUMBER: P246953

CATALOG NUMBER: LD8B120D010 ER8B120827 8LBM0LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	19508.6
2.5°	19288.8
5°	18624.1
7.5°	17554.4
10°	16234.6
12.5°	14818.0
15°	13419.4
17.5°	12012.5
20°	10718.9
22.5°	9515.2
25°	8379.2
27.5°	7186.5
30°	5927.5
32.5°	4611.8
35°	3374.9
37.5°	2261.0
40°	1405.5
42.5°	840.3
45°	504.4
47.5°	280.6
50°	164.5
52.5°	87.1
55°	42.8
57.5°	30.4
60°	26.3
62.5°	12.4
65°	16.6
67.5°	16.6
70°	1.4
72.5°	4.1
75°	5.5
77.5°	2.8
80°	0.0
82.5°	1.4
85°	5.5
87.5°	0.0
90°	0.0

(END OF REPORT)