

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P247049

Luminaire Tested: **LD8B120D010 ER8B120827 8LBW0LI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P247049
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P25264)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B120D010 ER8B120827 8LBW0LI
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 2700 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12321.1 lumens
Efficiency: N/A
Efficacy: 104.2 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.22
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 118.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P247049

CATALOG NUMBER: LD8B120D010 ER8B120827 8LBW0LI

Luminous Intensity Polar Plot





TEST NUMBER: P247049

CATALOG NUMBER: LD8B120D010 ER8B120827 8LBW0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	94	92
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75
4	93	84	78	73	91	83	77	72	81	75	71	79	74	70	77	73	70	68
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51
8	72	61	54	49	71	60	54	49	59	53	49	58	52	48	57	52	48	47
9	68	56	50	45	66	56	49	45	55	49	45	54	48	45	53	48	44	43
10	64	53	46	41	63	52	46	41	51	45	41	50	45	41	50	45	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	212012
5°	216146
10°	225418
15°	238157
20°	247083
25°	248876
30°	237109
35°	209144
40°	168600
45°	119703
50°	71940
55°	32413
60°	8357
65°	1802
70°	893
75°	596
80°	302
85°	0



TEST NUMBER: P247049

CATALOG NUMBER: LD8B120D010 ER8B120827 8LBW0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	673.6	5.5
10°-20°	2109.1	17.1
20°-30°	3335.5	27.1
30°-40°	3427.3	27.8
40°-50°	2126.0	17.3
50°-60°	602.7	4.9
60°-70°	40.7	0.3
70°-80°	5.5	0.0
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6118.2	49.7
0°-40°	9545.4	77.5
0°-60°	12274.2	99.6
0°-90°	12321.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	12321.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6875	
5°	6983	674
15°	7460	2109
25°	7315	3335
35°	5556	3427
45°	2745	2126
55°	603	603
65°	25	41
75°	5	5
85°	0	1
90°	0	



TEST NUMBER: P247049

CATALOG NUMBER: LD8B120D010 ER8B120827 8LBW0LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	6875.4
2.5°	6888.6
5°	6982.8
7.5°	7093.4
10°	7199.1
12.5°	7329.6
15°	7460.1
17.5°	7534.3
20°	7529.5
22.5°	7456.7
25°	7314.7
27.5°	7057.1
30°	6659.1
32.5°	6135.5
35°	5555.8
37.5°	4900.2
40°	4188.4
42.5°	3448.4
45°	2744.9
47.5°	2090.9
50°	1499.6
52.5°	1009.2
55°	602.9
57.5°	310.5
60°	135.5
62.5°	54.6
65°	24.7
67.5°	14.9
70°	9.9
72.5°	6.7
75°	5.0
77.5°	3.3
80°	1.7
82.5°	1.7
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)