

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P249878

Luminaire Tested: **LD8B120D010 ER8B120830 8LBM0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P249878
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13954)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B120D010 ER8B120830 8LBM0H
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
80 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 11528.0 lumens
Efficiency: N/A
Efficacy: 97.4 lumens/watt
Spacing Criteria (0/90/45): 0.92 / 0.92 / 0.93
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 118.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P249878

CATALOG NUMBER: LD8B120D010 ER8B120830 8LBM0H

Luminous Intensity Polar Plot





TEST NUMBER: P249878

CATALOG NUMBER: LD8B120D010 ER8B120830 8LBM0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1 | 113 | 110 | 108 | 105 | 111 | 108 | 106 | 104 | 104 | 102 | 101 | 100 | 99 | 98 | 97 | 96 | 95 | 93 |
| 2 | 107 | 102 | 98 | 94 | 105 | 100 | 97 | 93 | 97 | 94 | 91 | 94 | 92 | 89 | 91 | 89 | 87 | 86 |
| 3 | 101 | 95 | 90 | 85 | 99 | 93 | 89 | 85 | 91 | 87 | 83 | 88 | 85 | 82 | 86 | 83 | 81 | 79 |
| 4 | 96 | 88 | 82 | 78 | 94 | 87 | 82 | 77 | 85 | 80 | 76 | 83 | 79 | 76 | 81 | 77 | 75 | 73 |
| 5 | 91 | 82 | 76 | 71 | 89 | 81 | 75 | 71 | 79 | 74 | 70 | 78 | 73 | 70 | 76 | 72 | 69 | 68 |
| 6 | 86 | 77 | 70 | 66 | 84 | 76 | 70 | 66 | 74 | 69 | 65 | 73 | 68 | 65 | 71 | 67 | 64 | 63 |
| 7 | 81 | 72 | 65 | 61 | 80 | 71 | 65 | 61 | 70 | 64 | 60 | 68 | 64 | 60 | 67 | 63 | 60 | 58 |
| 8 | 77 | 67 | 61 | 57 | 76 | 67 | 61 | 56 | 65 | 60 | 56 | 64 | 60 | 56 | 63 | 59 | 56 | 54 |
| 9 | 73 | 63 | 57 | 53 | 72 | 63 | 57 | 53 | 62 | 56 | 53 | 61 | 56 | 52 | 60 | 55 | 52 | 51 |
| 10 | 70 | 60 | 53 | 49 | 69 | 59 | 53 | 49 | 58 | 53 | 49 | 57 | 53 | 49 | 57 | 52 | 49 | 48 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|--------|
| | 0° |
| 0° | 372074 |
| 5° | 366596 |
| 10° | 342128 |
| 15° | 314037 |
| 20° | 292483 |
| 25° | 270226 |
| 30° | 229154 |
| 35° | 164851 |
| 40° | 97113 |
| 45° | 51899 |
| 50° | 27081 |
| 55° | 15268 |
| 60° | 8424 |
| 65° | 4984 |
| 70° | 2272 |
| 75° | 1287 |
| 80° | 639 |
| 85° | 0 |



TEST NUMBER: P249878

CATALOG NUMBER: LD8B120D010 ER8B120830 8LBM0H

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|---------|-----------|
| 0°-10° | 1100.0 | 9.5 |
| 10°-20° | 2767.7 | 24.0 |
| 20°-30° | 3593.0 | 31.2 |
| 30°-40° | 2711.9 | 23.5 |
| 40°-50° | 992.3 | 8.6 |
| 50°-60° | 277.4 | 2.4 |
| 60°-70° | 72.9 | 0.6 |
| 70°-80° | 12.3 | 0.1 |
| 80°-90° | 0.5 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 7460.7 | 64.7 |
| 0°-40° | 10172.6 | 88.2 |
| 0°-60° | 11442.3 | 99.3 |
| 0°-90° | 11528.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 11528.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-------|------|
| 0° | 12066 | |
| 5° | 11843 | ### |
| 15° | 9837 | 2768 |
| 25° | 7942 | 3593 |
| 35° | 4379 | 2712 |
| 45° | 1190 | 992 |
| 55° | 284 | 277 |
| 65° | 68 | 73 |
| 75° | 11 | 12 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P249878

CATALOG NUMBER: LD8B120D010 ER8B120830 8LBM0H

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|---------|
| 0° | 12066.1 |
| 1° | 12084.1 |
| 2° | 12069.7 |
| 3° | 12023.0 |
| 4° | 11943.9 |
| 5° | 11843.2 |
| 6° | 11695.8 |
| 7° | 11534.0 |
| 8° | 11347.0 |
| 9° | 11142.1 |
| 10° | 10926.4 |
| 11° | 10710.7 |
| 12° | 10487.7 |
| 13° | 10261.2 |
| 14° | 10045.5 |
| 15° | 9837.0 |
| 16° | 9639.2 |
| 17° | 9448.7 |
| 18° | 9276.1 |
| 19° | 9096.3 |
| 20° | 8913.0 |
| 22.5° | 8456.4 |
| 25° | 7942.2 |
| 27.5° | 7262.7 |
| 30° | 6435.7 |
| 32.5° | 5439.8 |
| 35° | 4379.2 |
| 37.5° | 3343.7 |
| 40° | 2412.5 |
| 42.5° | 1707.8 |
| 45° | 1190.1 |
| 47.5° | 837.7 |
| 50° | 564.5 |
| 52.5° | 413.5 |
| 55° | 284.0 |
| 57.5° | 204.9 |
| 60° | 136.6 |
| 62.5° | 100.7 |
| 65° | 68.3 |
| 67.5° | 46.7 |
| 70° | 25.2 |
| 72.5° | 18.0 |
| 75° | 10.8 |
| 77.5° | 3.6 |
| 80° | 3.6 |



TEST NUMBER: P249878

CATALOG NUMBER: LD8B120D010 ER8B120830 8LBM0H

CANDELA DISTRIBUTION (continued):

| | 0° |
|-------|-----|
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)