

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245808

Luminaire Tested: **LD8B10D010 ER8B10930 8LBS0GPH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P245808  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-16)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B10D010 ER8B10930 8LBS0GPH  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
97 CRI 3000 CCT WITH GRAPHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 929.3 lumens  
Efficiency: N/A  
Efficacy: 91.1 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 10.2  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P245808

CATALOG NUMBER: LD8B10D010 ER8B10930 8LBS0GPH

### Luminous Intensity Polar Plot





TEST NUMBER: P245808

CATALOG NUMBER: LD8B10D010 ER8B10930 8LBS0GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77		83	79	76		81	77	74	73
4	91	82	75	70	89	81	74	69	78	73	69		76	72	68		74	70	67	65
5	85	75	68	62	83	74	67	62	72	66	61		70	65	61		68	64	60	58
6	79	69	61	56	78	68	61	56	66	60	55		64	59	55		63	58	54	53
7	74	63	56	50	73	62	55	50	61	55	50		59	54	50		58	53	49	48
8	70	58	51	46	68	57	50	46	56	50	45		55	49	45		54	49	45	43
9	65	54	47	42	64	53	46	42	52	46	41		51	45	41		50	45	41	40
10	62	50	43	38	60	49	43	38	48	42	38		48	42	38		47	42	38	36

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P245808

CATALOG NUMBER: LD8B10D010 ER8B10930 8LBS0GPH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	50.2	5.4
10°-20°	142.0	15.3
20°-30°	211.4	22.7
30°-40°	240.3	25.9
40°-50°	196.4	21.1
50°-60°	73.2	7.9
60°-70°	13.4	1.4
70°-80°	2.1	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	403.6	43.4
0°-40°	643.8	69.3
0°-60°	913.5	98.3
0°-90°	929.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	929.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	533	
5°	530	50
15°	503	142
25°	460	211
35°	386	240
45°	261	196
55°	75	73
65°	12	13
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P245808

CATALOG NUMBER: LD8B10D010 ER8B10930 8LBS0GPH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	533.4
2.5°	532.5
5°	529.8
7.5°	525.0
10°	518.6
12.5°	511.3
15°	503.4
17.5°	494.2
20°	484.6
22.5°	473.1
25°	459.7
27.5°	444.6
30°	427.3
32.5°	407.6
35°	385.7
37.5°	362.4
40°	335.4
42.5°	302.0
45°	261.4
47.5°	212.5
50°	161.3
52.5°	113.7
55°	75.2
57.5°	47.3
60°	29.4
62.5°	18.8
65°	12.1
67.5°	7.0
70°	3.9
72.5°	2.5
75°	1.8
77.5°	1.2
80°	0.9
82.5°	0.3
85°	0.3
87.5°	0.0
90°	0.0

(END OF REPORT)