

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243864

Luminaire Tested: **LD8B10D010 ER8B10930 8LBWOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P243864
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27941)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B10930 8LBW0LI
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 992.0 lumens
Efficiency: N/A
Efficacy: 97.3 lumens/watt
Spacing Criteria (0/90/45): 1.34 / 1.34 / 1.17
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct

Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P243864
CATALOG NUMBER: LD8B10D010 ER8B10930 8LBW0LI

Luminous Intensity Polar Plot





TEST NUMBER: P243864

CATALOG NUMBER: LD8B10D010 ER8B10930 8LBW0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96	95	94	92
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90	88	86	84
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84	81	78	77
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78	75	72	70
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73	69	65	64
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63	59	55	54
8	74	63	56	52	72	62	56	52	61	55	51		60	55	51		59	54	51	49
9	70	59	52	48	68	58	52	47	57	51	47		56	51	47		55	50	47	45
10	66	55	48	44	65	54	48	44	53	48	44		53	47	44		52	47	43	42

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P243864

CATALOG NUMBER: LD8B10D010 ER8B10930 8LBW0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.2	5.8
10°-20°	189.6	19.1
20°-30°	298.4	30.1
30°-40°	283.8	28.6
40°-50°	130.9	13.2
50°-60°	29.7	3.0
60°-70°	2.0	0.2
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	545.3	55.0
0°-40°	829.1	83.6
0°-60°	989.7	99.8
0°-90°	992.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	992.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	571	
5°	586	57
15°	673	190
25°	654	298
35°	465	284
45°	160	131
55°	29	30
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P243864

CATALOG NUMBER: LD8B10D010 ER8B10930 8LBW0LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	570.8
1°	570.6
2°	571.6
3°	574.8
4°	579.8
5°	585.5
6°	592.6
7°	600.2
8°	608.0
9°	617.2
10°	627.0
11°	636.7
12°	647.0
13°	656.9
14°	665.8
15°	672.8
16°	678.0
17°	681.6
18°	683.1
19°	682.9
20°	681.0
21°	677.8
22°	673.7
23°	668.2
24°	662.1
25°	654.4
26°	645.5
27°	634.0
28°	620.5
29°	604.8
30°	586.5
32.5°	532.0
35°	465.2
37.5°	387.6
40°	302.9
42.5°	224.0
45°	160.2
47.5°	113.4
50°	78.1
52.5°	50.0
55°	28.8
57.5°	14.3
60°	6.3
62.5°	2.5
65°	1.3



TEST NUMBER: P243864

CATALOG NUMBER: LD8B10D010 ER8B10930 8LBW0LI

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.8
70°	0.6
72.5°	0.6
75°	0.2
77.5°	0.2
80°	0.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)