

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244728

Luminaire Tested: **LD8B10D010 ER8B10930 8LBW0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244728
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-44)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B10930 8LBW0WMH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 910.2 lumens
Efficiency: N/A
Efficacy: 89.2 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.06
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244728

CATALOG NUMBER: LD8B10D010 ER8B10930 8LBW0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244728

CATALOG NUMBER: LD8B10D010 ER8B10930 8LBW0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89	87	84	83
3	99	91	86	81	97	90	85	80	87	83	79		85	81	78		82	79	76	75
4	93	84	77	72	91	83	77	72	80	75	71		78	74	70		76	73	69	68
5	87	77	70	65	85	76	70	65	74	69	64		73	68	64		71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59		67	62	58		66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61	57	53	51
8	72	61	54	50	71	61	54	50	60	54	49		58	53	49		57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46		55	49	45		54	49	45	44
10	65	54	47	42	63	53	47	42	52	46	42		51	46	42		51	46	42	41

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P244728

CATALOG NUMBER: LD8B10D010 ER8B10930 8LBW0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.6	6.7
10°-20°	168.5	18.5
20°-30°	251.0	27.6
30°-40°	233.1	25.6
40°-50°	110.1	12.1
50°-60°	59.1	6.5
60°-70°	23.7	2.6
70°-80°	3.7	0.4
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	480.1	52.7
0°-40°	713.1	78.4
0°-60°	882.4	96.9
0°-90°	910.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	910.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	660	
5°	644	61
15°	596	169
25°	549	251
35°	387	233
45°	134	110
55°	65	59
65°	24	24
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P244728

CATALOG NUMBER: LD8B10D010 ER8B10930 8LBW0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	659.7
2.5°	655.1
5°	643.9
7.5°	629.8
10°	616.4
12.5°	605.6
15°	596.5
17.5°	587.1
20°	576.8
22.5°	565.0
25°	549.3
27.5°	527.2
30°	496.6
32.5°	451.9
35°	387.4
37.5°	305.1
40°	226.2
42.5°	168.5
45°	134.3
47.5°	112.2
50°	94.7
52.5°	78.9
55°	65.0
57.5°	52.9
60°	42.9
62.5°	33.5
65°	23.5
67.5°	13.9
70°	8.2
72.5°	4.8
75°	3.0
77.5°	1.8
80°	0.9
82.5°	0.6
85°	0.3
87.5°	0.0
90°	0.0

(END OF REPORT)