

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P247053

Luminaire Tested: **LD8B120D010 ER8B120830 8LBW0LI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P247053
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P25264)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B120D010 ER8B120830 8LBW0LI
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3000 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12629.0 lumens
Efficiency: N/A
Efficacy: 106.8 lumens/watt
Spacing Criteria (0/90/45): 1.32 / 1.32 / 1.22
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 118.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P247053

CATALOG NUMBER: LD8B120D010 ER8B120830 8LBW0LI

Luminous Intensity Polar Plot





TEST NUMBER: P247053

CATALOG NUMBER: LD8B120D010 ER8B120830 8LBW0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99	99	98	96	96	95	94	92
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83
3	99	92	86	81	97	90	85	81	88	83	79	85	81	78	83	80	77	75
4	93	84	78	73	91	83	77	72	81	75	71	79	74	70	77	73	70	68
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51
8	72	61	54	49	71	60	54	49	59	53	49	58	52	48	57	52	48	47
9	68	56	50	45	66	56	49	45	55	49	45	54	48	45	53	48	44	43
10	64	53	46	41	63	52	46	41	51	45	41	50	45	41	50	45	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	217310
5°	221551
10°	231051
15°	244108
20°	253259
25°	255099
30°	243037
35°	214372
40°	172814
45°	122694
50°	73739
55°	33219
60°	8566
65°	1846
70°	911
75°	608
80°	302
85°	0



TEST NUMBER: P247053

CATALOG NUMBER: LD8B120D010 ER8B120830 8LBW0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	690.4	5.5
10°-20°	2161.9	17.1
20°-30°	3418.8	27.1
30°-40°	3513.0	27.8
40°-50°	2179.2	17.3
50°-60°	617.8	4.9
60°-70°	41.7	0.3
70°-80°	5.6	0.0
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6271.1	49.7
0°-40°	9784.1	77.5
0°-60°	12581.0	99.6
0°-90°	12629.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	12629.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7047	
5°	7157	690
15°	7646	2162
25°	7498	3419
35°	5695	3513
45°	2814	2179
55°	618	618
65°	25	42
75°	5	6
85°	0	1
90°	0	



TEST NUMBER: P247053

CATALOG NUMBER: LD8B120D010 ER8B120830 8LBW0LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	7047.2
2.5°	7060.8
5°	7157.4
7.5°	7270.8
10°	7379.0
12.5°	7512.8
15°	7646.5
17.5°	7722.7
20°	7717.7
22.5°	7643.1
25°	7497.6
27.5°	7233.5
30°	6825.6
32.5°	6288.9
35°	5694.7
37.5°	5022.7
40°	4293.1
42.5°	3534.6
45°	2813.5
47.5°	2143.2
50°	1537.1
52.5°	1034.4
55°	617.9
57.5°	318.3
60°	138.9
62.5°	55.9
65°	25.3
67.5°	15.2
70°	10.1
72.5°	6.8
75°	5.1
77.5°	3.4
80°	1.7
82.5°	1.7
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)