

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243840

Luminaire Tested: **LD8B10D010 ER8B10935 8LBWOLI**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P243840
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27941)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B10935 8LBW0LI
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 3500 CCT WITH SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1024.0 lumens
Efficiency: N/A
Efficacy: 100.4 lumens/watt
Spacing Criteria (0/90/45): 1.34 / 1.34 / 1.17
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P243840

CATALOG NUMBER: LD8B10D010 ER8B10935 8LBW0LI

Luminous Intensity Polar Plot





TEST NUMBER: P243840

CATALOG NUMBER: LD8B10D010 ER8B10935 8LBW0LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96	95	94	92
2	106	101	97	93	104	99	95	92	96	93	90		93	90	88		90	88	86	84
3	100	93	87	83	98	92	86	82	89	85	81		86	83	80		84	81	78	77
4	94	86	79	75	92	84	79	74	82	77	73		80	76	72		78	75	72	70
5	88	79	72	68	87	78	72	67	76	71	67		74	70	66		73	69	65	64
6	83	73	66	62	82	72	66	61	71	65	61		69	64	60		68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63	59	55	54
8	74	63	56	52	72	62	56	52	61	55	51		60	55	51		59	54	51	49
9	70	59	52	48	68	58	52	47	57	51	47		56	51	47		55	50	47	45
10	66	55	48	44	65	54	48	44	53	48	44		53	47	44		52	47	43	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	18169
5°	18706
10°	20265
15°	22171
20°	23066
25°	22983
30°	21556
35°	18077
40°	12587
45°	7209
50°	3871
55°	1597
60°	395
65°	102
70°	54
75°	36
80°	53
85°	0



TEST NUMBER: P243840

CATALOG NUMBER: LD8B10D010 ER8B10935 8LBW0LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.1	5.8
10°-20°	195.7	19.1
20°-30°	308.0	30.1
30°-40°	293.0	28.6
40°-50°	135.1	13.2
50°-60°	30.7	3.0
60°-70°	2.0	0.2
70°-80°	0.4	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	562.8	55.0
0°-40°	855.8	83.6
0°-60°	1021.5	99.8
0°-90°	1024.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1024.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	589	
5°	604	59
15°	694	196
25°	676	308
35°	480	293
45°	165	135
55°	30	31
65°	1	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P243840

CATALOG NUMBER: LD8B10D010 ER8B10935 8LBW0LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	589.2
1°	588.9
2°	590.0
3°	593.4
4°	598.4
5°	604.3
6°	611.6
7°	619.4
8°	627.6
9°	637.1
10°	647.2
11°	657.3
12°	667.9
13°	678.0
14°	687.2
15°	694.5
16°	699.8
17°	703.5
18°	705.2
19°	704.9
20°	702.9
21°	699.6
22°	695.4
23°	689.8
24°	683.3
25°	675.5
26°	666.2
27°	654.5
28°	640.4
29°	624.2
30°	605.4
32.5°	549.1
35°	480.2
37.5°	400.1
40°	312.7
42.5°	231.1
45°	165.3
47.5°	117.1
50°	80.7
52.5°	51.5
55°	29.7
57.5°	14.8
60°	6.4
62.5°	2.5
65°	1.4



TEST NUMBER: P243840

CATALOG NUMBER: LD8B10D010 ER8B10935 8LBW0LI

CANDELA DISTRIBUTION (continued):

	0°
67.5°	0.8
70°	0.6
72.5°	0.6
75°	0.3
77.5°	0.3
80°	0.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)