

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250396

Luminaire Tested: **LD8B120D010 ER8B120840 8LBN0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250396
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13948)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B120D010 ER8B120840 8LBN0B
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 4000 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7233.0 lumens
Efficiency: N/A
Efficacy: 61.1 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 118.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250396

CATALOG NUMBER: LD8B120D010 ER8B120840 8LBN0B

Luminous Intensity Polar Plot





TEST NUMBER: P250396

CATALOG NUMBER: LD8B120D010 ER8B120840 8LBNOB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102		101	100	99		98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72		79	75	71		77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74	70	67	66
8	83	74	68	64	81	73	68	64	72	67	64		71	67	64		70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61		68	63	60		67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57		65	60	57		64	60	57	56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	356394
5°	350701
10°	311589
15°	257034
20°	216473
25°	182584
30°	136708
35°	77366
40°	30593
45°	8212
50°	1574
55°	0
60°	228
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P250396

CATALOG NUMBER: LD8B120D010 ER8B120840 8LBN0B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1037.5	14.3
10°-20°	2255.0	31.2
20°-30°	2420.9	33.5
30°-40°	1308.4	18.1
40°-50°	204.1	2.8
50°-60°	5.6	0.1
60°-70°	1.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5713.4	79.0
0°-40°	7021.9	97.1
0°-60°	7231.6	100.0
0°-90°	7233.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7233.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11558	
5°	11330	###
15°	8051	2255
25°	5366	2421
35°	2055	1308
45°	188	204
55°	0	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P250396

CATALOG NUMBER: LD8B120D010 ER8B120840 8LBNOB

CANDELA DISTRIBUTION (FULL):

	0°
0°	11557.6
1°	11579.5
2°	11568.7
3°	11529.1
4°	11453.0
5°	11329.7
6°	11160.0
7°	10931.6
8°	10645.8
9°	10316.9
10°	9951.1
11°	9567.4
12°	9169.4
13°	8771.7
14°	8402.3
15°	8051.4
16°	7729.3
17°	7418.0
18°	7128.5
19°	6857.5
20°	6596.7
21°	6343.3
22°	6104.3
23°	5865.9
24°	5616.2
25°	5366.3
26°	5112.9
27°	4823.6
28°	4505.0
29°	4179.8
30°	3839.4
31°	3474.0
32°	3108.2
33°	2746.5
34°	2381.0
35°	2055.2
37.5°	1313.5
40°	760.0
42.5°	405.4
45°	188.3
47.5°	101.5
50°	32.8
52.5°	3.7
55°	0.0
57.5°	3.7



TEST NUMBER: P250396

CATALOG NUMBER: LD8B120D010 ER8B120840 8LBN0B

CANDELA DISTRIBUTION (continued):

	0°
60°	3.7
62.5°	0.0
65°	0.0
67.5°	3.7
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)