

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244782

Luminaire Tested: **LD8B10D010 ER8B10940 8LBN0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244782
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201884)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B10940 8LBN0WMH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 4000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 906.0 lumens
Efficiency: N/A
Efficacy: 88.8 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.79
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244782

CATALOG NUMBER: LD8B10D010 ER8B10940 8LBN0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244782

CATALOG NUMBER: LD8B10D010 ER8B10940 8LBN0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | | 50 | 30 | 10 | | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | | 106 | 106 | 106 | | 102 | 102 | 102 | 100 |
| 1 | 114 | 111 | 109 | 107 | 111 | 109 | 107 | 105 | 105 | 103 | 102 | | 101 | 100 | 99 | | 98 | 97 | 96 | 94 |
| 2 | 108 | 104 | 100 | 97 | 106 | 102 | 99 | 96 | 99 | 96 | 93 | | 96 | 94 | 91 | | 93 | 91 | 90 | 88 |
| 3 | 103 | 97 | 92 | 89 | 101 | 96 | 91 | 88 | 93 | 89 | 86 | | 91 | 88 | 85 | | 89 | 86 | 84 | 82 |
| 4 | 98 | 91 | 86 | 82 | 97 | 90 | 85 | 81 | 88 | 84 | 80 | | 86 | 82 | 79 | | 84 | 81 | 79 | 77 |
| 5 | 94 | 86 | 80 | 76 | 92 | 85 | 80 | 76 | 83 | 78 | 75 | | 81 | 77 | 74 | | 80 | 76 | 74 | 72 |
| 6 | 89 | 81 | 75 | 71 | 88 | 80 | 75 | 71 | 79 | 74 | 70 | | 77 | 73 | 70 | | 76 | 72 | 69 | 68 |
| 7 | 85 | 76 | 71 | 67 | 84 | 76 | 70 | 66 | 74 | 70 | 66 | | 73 | 69 | 66 | | 72 | 68 | 65 | 64 |
| 8 | 81 | 72 | 66 | 63 | 80 | 72 | 66 | 62 | 71 | 66 | 62 | | 70 | 65 | 62 | | 69 | 65 | 62 | 60 |
| 9 | 78 | 68 | 63 | 59 | 77 | 68 | 63 | 59 | 67 | 62 | 59 | | 66 | 62 | 59 | | 65 | 61 | 58 | 57 |
| 10 | 74 | 65 | 59 | 56 | 73 | 65 | 59 | 56 | 64 | 59 | 56 | | 63 | 59 | 55 | | 62 | 58 | 55 | 54 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 40685 |
| 5° | 40120 |
| 10° | 36707 |
| 15° | 31515 |
| 20° | 26541 |
| 25° | 21922 |
| 30° | 16447 |
| 35° | 9803 |
| 40° | 4669 |
| 45° | 2037 |
| 50° | 916 |
| 55° | 403 |
| 60° | 241 |
| 65° | 131 |
| 70° | 135 |
| 75° | 0 |
| 80° | 53 |
| 85° | 212 |



TEST NUMBER: P244782

CATALOG NUMBER: LD8B10D010 ER8B10940 8LBN0WMH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 119.7 | 13.2 |
| 10°-20° | 275.1 | 30.4 |
| 20°-30° | 291.9 | 32.2 |
| 30°-40° | 166.5 | 18.4 |
| 40°-50° | 41.3 | 4.6 |
| 50°-60° | 8.1 | 0.9 |
| 60°-70° | 2.4 | 0.3 |
| 70°-80° | 0.6 | 0.1 |
| 80°-90° | 0.4 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 686.7 | 75.8 |
| 0°-40° | 853.2 | 94.2 |
| 0°-60° | 902.6 | 99.6 |
| 0°-90° | 906.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 906.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|------|------|------|
| 0° | 1319 | |
| 5° | 1296 | 120 |
| 15° | 987 | 275 |
| 25° | 644 | 292 |
| 35° | 260 | 167 |
| 45° | 47 | 41 |
| 55° | 8 | 8 |
| 65° | 2 | 2 |
| 75° | 0 | 1 |
| 85° | 1 | 0 |
| 90° | 0 | 0 |
| 95° | 0 | 0 |
| 105° | 0 | 0 |
| 115° | 0 | 0 |
| 125° | 0 | 0 |
| 135° | 0 | 0 |
| 145° | 0 | 0 |
| 155° | 0 | 0 |
| 165° | 0 | 0 |
| 175° | 0 | 0 |
| 180° | 0 | 0 |



TEST NUMBER: P244782

CATALOG NUMBER: LD8B10D010 ER8B10940 8LBN0WMH

CANDELA DISTRIBUTION (FULL):

| 0° | |
|--------|--------|
| 0° | 1319.4 |
| 2.5° | 1318.8 |
| 5° | 1296.1 |
| 7.5° | 1246.1 |
| 10° | 1172.3 |
| 12.5° | 1083.2 |
| 15° | 987.2 |
| 17.5° | 895.8 |
| 20° | 808.8 |
| 22.5° | 725.1 |
| 25° | 644.3 |
| 27.5° | 557.6 |
| 30° | 461.9 |
| 32.5° | 359.1 |
| 35° | 260.4 |
| 37.5° | 179.4 |
| 40° | 116.0 |
| 42.5° | 73.5 |
| 45° | 46.7 |
| 47.5° | 30.5 |
| 50° | 19.1 |
| 52.5° | 11.6 |
| 55° | 7.5 |
| 57.5° | 6.0 |
| 60° | 3.9 |
| 62.5° | 3.6 |
| 65° | 1.8 |
| 67.5° | 1.8 |
| 70° | 1.5 |
| 72.5° | 0.9 |
| 75° | 0.0 |
| 77.5° | 0.3 |
| 80° | 0.3 |
| 82.5° | 0.6 |
| 85° | 0.6 |
| 87.5° | 0.3 |
| 90° | 0.0 |
| 92.5° | 0.0 |
| 95° | 0.0 |
| 97.5° | 0.0 |
| 100° | 0.0 |
| 102.5° | 0.0 |
| 105° | 0.0 |
| 107.5° | 0.0 |
| 110° | 0.0 |



TEST NUMBER: P244782

CATALOG NUMBER: LD8B10D010 ER8B10940 8LBN0WMH

CANDELA DISTRIBUTION (continued):

| | 0° |
|--------|-----|
| 112.5° | 0.0 |
| 115° | 0.0 |
| 117.5° | 0.0 |
| 120° | 0.0 |
| 122.5° | 0.0 |
| 125° | 0.0 |
| 127.5° | 0.0 |
| 130° | 0.0 |
| 132.5° | 0.0 |
| 135° | 0.0 |
| 137.5° | 0.0 |
| 140° | 0.0 |
| 142.5° | 0.0 |
| 145° | 0.0 |
| 147.5° | 0.0 |
| 150° | 0.0 |
| 152.5° | 0.0 |
| 155° | 0.0 |
| 157.5° | 0.0 |
| 160° | 0.0 |
| 162.5° | 0.0 |
| 165° | 0.0 |
| 167.5° | 0.0 |
| 170° | 0.0 |
| 172.5° | 0.0 |
| 175° | 0.0 |
| 177.5° | 0.0 |
| 180° | 0.0 |

(END OF REPORT)