

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244710

Luminaire Tested: **LD8B10D010 ER8B10940 8LBW0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244710
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-44)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B10940 8LBW0WMH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 4000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 982.0 lumens
Efficiency: N/A
Efficacy: 96.3 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244710

CATALOG NUMBER: LD8B10D010 ER8B10940 8LBW0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244710

CATALOG NUMBER: LD8B10D010 ER8B10940 8LBW0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89	86	84	83
3	99	91	86	81	97	90	85	80	87	83	79		85	81	78		82	79	76	75
4	93	84	77	72	91	83	77	72	80	75	71		78	74	70		76	73	69	68
5	87	77	70	65	85	76	70	65	74	69	64		73	68	64		71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59		67	62	58		66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		61	57	53	51
8	72	61	54	50	71	61	54	50	60	54	49		58	53	49		57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46		55	49	45		54	49	45	44
10	65	54	47	42	63	53	47	42	52	46	42		51	46	42		51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	21946
5°	21504
10°	20822
15°	20543
20°	20421
25°	20163
30°	19078
35°	15735
40°	9826
45°	6319
50°	4898
55°	3774
60°	2855
65°	1861
70°	793
75°	393
80°	178
85°	106



TEST NUMBER: P244710

CATALOG NUMBER: LD8B10D010 ER8B10940 8LBW0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.3	6.7
10°-20°	181.8	18.5
20°-30°	270.8	27.6
30°-40°	251.5	25.6
40°-50°	118.8	12.1
50°-60°	63.8	6.5
60°-70°	25.6	2.6
70°-80°	4.0	0.4
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	517.9	52.7
0°-40°	769.4	78.3
0°-60°	952.0	96.9
0°-90°	982.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	982.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	712	
5°	695	65
15°	644	182
25°	593	271
35°	418	251
45°	145	119
55°	70	64
65°	26	26
75°	3	4
85°	0	0
90°	0	



TEST NUMBER: P244710

CATALOG NUMBER: LD8B10D010 ER8B10940 8LBW0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	711.7
2.5°	706.8
5°	694.7
7.5°	679.4
10°	665.0
12.5°	653.3
15°	643.5
17.5°	633.3
20°	622.3
22.5°	609.5
25°	592.6
27.5°	568.7
30°	535.8
32.5°	487.5
35°	418.0
37.5°	329.2
40°	244.1
42.5°	181.7
45°	144.9
47.5°	121.1
50°	102.1
52.5°	85.2
55°	70.2
57.5°	57.1
60°	46.3
62.5°	36.2
65°	25.5
67.5°	15.0
70°	8.8
72.5°	5.2
75°	3.3
77.5°	2.0
80°	1.0
82.5°	0.7
85°	0.3
87.5°	0.0
90°	0.0

(END OF REPORT)