

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245796

Luminaire Tested: **LD8B10D010 ER8B10950 8LBS0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245796
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-16)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B10950 8LBS0GPH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 5000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1038.0 lumens
Efficiency: N/A
Efficacy: 101.8 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245796

CATALOG NUMBER: LD8B10D010 ER8B10950 8LBS0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P245796

CATALOG NUMBER: LD8B10D010 ER8B10950 8LBS0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87		91	88	85		88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77		83	79	76		81	77	74	73
4	91	82	75	70	89	81	74	69	78	73	69		76	72	68		74	70	67	65
5	85	75	68	62	83	74	67	62	72	66	61		70	65	61		68	64	60	58
6	79	69	61	56	78	68	61	56	66	60	55		64	59	55		63	58	54	53
7	74	63	56	50	73	62	55	50	61	55	50		59	54	50		58	53	49	48
8	70	58	51	46	68	57	50	46	56	50	45		55	49	45		54	49	45	43
9	65	54	47	42	64	53	46	42	52	46	41		51	45	41		50	45	41	40
10	62	50	43	38	60	49	43	38	48	42	38		48	42	38		47	42	38	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	18372
5°	18316
10°	18136
15°	17951
20°	17763
25°	17471
30°	16995
35°	16221
40°	15079
45°	12734
50°	8645
55°	4516
60°	2029
65°	985
70°	397
75°	238
80°	178
85°	106



TEST NUMBER: P245796

CATALOG NUMBER: LD8B10D010 ER8B10950 8LBS0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.1	5.4
10°-20°	158.6	15.3
20°-30°	236.1	22.7
30°-40°	268.4	25.9
40°-50°	219.5	21.1
50°-60°	81.8	7.9
60°-70°	14.9	1.4
70°-80°	2.3	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	450.8	43.4
0°-40°	719.2	69.3
0°-60°	1020.4	98.3
0°-90°	1038.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1038.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	596	
5°	592	56
15°	562	159
25°	514	236
35°	431	268
45°	292	219
55°	84	82
65°	14	15
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P245796

CATALOG NUMBER: LD8B10D010 ER8B10950 8LBS0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	595.8
2.5°	594.8
5°	591.7
7.5°	586.3
10°	579.2
12.5°	571.1
15°	562.3
17.5°	552.1
20°	541.3
22.5°	528.4
25°	513.5
27.5°	496.6
30°	477.3
32.5°	455.2
35°	430.9
37.5°	404.8
40°	374.6
42.5°	337.4
45°	292.0
47.5°	237.4
50°	180.2
52.5°	127.0
55°	84.0
57.5°	52.8
60°	32.9
62.5°	21.0
65°	13.5
67.5°	7.8
70°	4.4
72.5°	2.7
75°	2.0
77.5°	1.4
80°	1.0
82.5°	0.3
85°	0.3
87.5°	0.0
90°	0.0

(END OF REPORT)