

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245580

Luminaire Tested: **LD8B10D010 ER8B10950 8LBW0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245580
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-46)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B10950 8LBW0GPH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 5000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 938.0 lumens
Efficiency: N/A
Efficacy: 92.0 lumens/watt
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245580

CATALOG NUMBER: LD8B10D010 ER8B10950 8LBW0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P245580

CATALOG NUMBER: LD8B10D010 ER8B10950 8LBW0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	108	105	103	103	101	100	100	98	97	96	95	94	92
2	106	101	96	92	104	99	95	91	96	92	89	93	90	87	90	88	86	84
3	100	93	87	83	98	91	86	82	89	84	81	86	82	79	84	81	78	76
4	94	85	79	74	92	84	78	74	82	77	73	80	76	72	78	74	71	70
5	88	79	72	67	87	78	72	67	76	71	66	74	70	66	73	69	65	64
6	83	73	66	61	82	72	66	61	71	65	61	69	64	60	68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56	65	59	56	63	59	55	54
8	74	63	56	52	73	63	56	52	61	56	51	60	55	51	59	55	51	49
9	70	59	52	48	69	58	52	48	57	52	48	57	51	47	56	51	47	46
10	66	55	49	44	65	55	49	44	54	48	44	53	48	44	52	47	44	43

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	22523
5°	21990
10°	21302
15°	20993
20°	20746
25°	20299
30°	19014
35°	15524
40°	9270
45°	5569
50°	4011
55°	2731
60°	1714
65°	839
70°	216
75°	83
80°	53
85°	0



TEST NUMBER: P245580

CATALOG NUMBER: LD8B10D010 ER8B10950 8LBW0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.8	7.1
10°-20°	185.6	19.8
20°-30°	272.5	29.1
30°-40°	247.0	26.3
40°-50°	105.8	11.3
50°-60°	46.8	5.0
60°-70°	12.5	1.3
70°-80°	1.0	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	524.9	56.0
0°-40°	772.0	82.3
0°-60°	924.5	98.6
0°-90°	938.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	938.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	730	
5°	710	67
15°	658	186
25°	597	273
35°	412	247
45°	128	106
55°	51	47
65°	12	12
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P245580

CATALOG NUMBER: LD8B10D010 ER8B10950 8LBW0GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	730.4
2.5°	724.6
5°	710.4
7.5°	694.1
10°	680.3
12.5°	668.7
15°	657.6
17.5°	645.7
20°	632.2
22.5°	616.3
25°	596.6
27.5°	570.2
30°	534.0
32.5°	483.2
35°	412.4
37.5°	319.6
40°	230.3
42.5°	166.3
45°	127.7
47.5°	102.9
50°	83.6
52.5°	66.4
55°	50.8
57.5°	37.9
60°	27.8
62.5°	19.3
65°	11.5
67.5°	5.1
70°	2.4
72.5°	1.4
75°	0.7
77.5°	0.3
80°	0.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)