

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245802

Luminaire Tested: **LD8B10D010 ER8B109727 8LBS0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245802
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-16)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B109727 8LBS0GPH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 784.0 lumens
Efficiency: N/A
Efficacy: 76.9 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245802

CATALOG NUMBER: LD8B10D010 ER8B109727 8LBS0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P245802

CATALOG NUMBER: LD8B10D010 ER8B109727 8LBS0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81
3	98	90	84	79	96	88	83	78	86	81	77	83	79	76	81	77	74	73
4	91	82	75	70	89	81	74	69	78	73	69	76	72	68	74	70	67	65
5	85	75	68	62	83	74	67	62	72	66	61	70	65	61	68	64	60	58
6	79	69	61	56	78	68	61	56	66	60	55	64	59	55	63	58	54	53
7	74	63	56	50	73	62	55	50	61	55	50	59	54	50	58	53	49	48
8	70	58	51	46	68	57	50	46	56	50	45	55	49	45	54	49	45	43
9	65	54	47	42	64	53	46	42	52	46	41	51	45	41	50	45	41	40
10	62	50	43	38	60	49	43	38	48	42	38	48	42	38	47	42	38	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	13876
5°	13833
10°	13699
15°	13558
20°	13415
25°	13195
30°	12836
35°	12249
40°	11392
45°	9616
50°	6529
55°	3408
60°	1529
65°	744
70°	298
75°	179
80°	142
85°	106



TEST NUMBER: P245802

CATALOG NUMBER: LD8B10D010 ER8B109727 8LBS0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.4	5.4
10°-20°	119.8	15.3
20°-30°	178.3	22.7
30°-40°	202.7	25.9
40°-50°	165.7	21.1
50°-60°	61.8	7.9
60°-70°	11.3	1.4
70°-80°	1.7	0.2
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	340.5	43.4
0°-40°	543.2	69.3
0°-60°	770.7	98.3
0°-90°	784.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	784.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	450	
5°	447	42
15°	425	120
25°	388	178
35°	325	203
45°	220	166
55°	63	62
65°	10	11
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P245802

CATALOG NUMBER: LD8B10D010 ER8B109727 8LBS0GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	450.0
2.5°	449.2
5°	446.9
7.5°	442.9
10°	437.5
12.5°	431.3
15°	424.7
17.5°	417.0
20°	408.8
22.5°	399.1
25°	387.8
27.5°	375.1
30°	360.5
32.5°	343.8
35°	325.4
37.5°	305.7
40°	283.0
42.5°	254.8
45°	220.5
47.5°	179.3
50°	136.1
52.5°	95.9
55°	63.4
57.5°	39.9
60°	24.8
62.5°	15.9
65°	10.2
67.5°	5.9
70°	3.3
72.5°	2.0
75°	1.5
77.5°	1.0
80°	0.8
82.5°	0.3
85°	0.3
87.5°	0.0
90°	0.0

(END OF REPORT)