

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244506

Luminaire Tested: **LD8B10D010 ER8B109727 8LBS0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244506
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-13)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B109727 8LBS0H
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 860.0 lumens
Efficiency: N/A
Efficacy: 84.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.23
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244506

CATALOG NUMBER: LD8B10D010 ER8B109727 8LBS0H

Luminous Intensity Polar Plot





TEST NUMBER: P244506

CATALOG NUMBER: LD8B10D010 ER8B109727 8LBS0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73
4	91	82	75	70	89	81	75	70	79	73	69	76	72	68	74	70	67	65
5	85	75	68	63	83	74	67	62	72	66	62	70	65	61	69	64	60	59
6	80	69	61	56	78	68	61	56	66	60	56	65	59	55	63	58	55	53
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48
8	70	58	51	46	68	58	51	46	57	50	46	55	50	46	54	49	45	44
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	15390
5°	15338
10°	15221
15°	15116
20°	15013
25°	14814
30°	14357
35°	13548
40°	12310
45°	10130
50°	6750
55°	3516
60°	1659
65°	868
70°	433
75°	298
80°	231
85°	177



TEST NUMBER: P244506

CATALOG NUMBER: LD8B10D010 ER8B109727 8LBS0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.0	5.5
10°-20°	133.6	15.5
20°-30°	199.9	23.2
30°-40°	223.6	26.0
40°-50°	175.4	20.4
50°-60°	64.0	7.4
60°-70°	13.1	1.5
70°-80°	2.8	0.3
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	380.5	44.2
0°-40°	604.1	70.2
0°-60°	843.5	98.1
0°-90°	860.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	860.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	499	
5°	496	47
15°	474	134
25°	435	200
35°	360	224
45°	232	175
55°	65	64
65°	12	13
75°	2	3
85°	0	1
90°	0	



TEST NUMBER: P244506

CATALOG NUMBER: LD8B10D010 ER8B109727 8LBS0H

CANDELA DISTRIBUTION (FULL):

	0°
0°	499.1
2.5°	498.3
5°	495.5
7.5°	491.5
10°	486.1
12.5°	480.1
15°	473.5
17.5°	466.1
20°	457.5
22.5°	447.3
25°	435.4
27.5°	420.7
30°	403.2
32.5°	382.7
35°	359.9
37.5°	334.2
40°	305.8
42.5°	272.1
45°	232.3
47.5°	187.4
50°	140.7
52.5°	98.6
55°	65.4
57.5°	41.8
60°	26.9
62.5°	17.8
65°	11.9
67.5°	7.6
70°	4.8
72.5°	3.3
75°	2.5
77.5°	1.8
80°	1.3
82.5°	0.8
85°	0.5
87.5°	0.3
90°	0.0

(END OF REPORT)