

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245370

Luminaire Tested: **LD8B10D010 ER8B109727 8LBS0WH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245370
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-15)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B109727 8LBS0WH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH WHEAT TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 844.0 lumens
Efficiency: N/A
Efficacy: 82.7 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.27 / 1.23
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245370

CATALOG NUMBER: LD8B10D010 ER8B109727 8LBS0WH

Luminous Intensity Polar Plot





TEST NUMBER: P245370

CATALOG NUMBER: LD8B10D010 ER8B109727 8LBS0WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | | 50 | 30 | 10 | | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | | 106 | 106 | 106 | | 102 | 102 | 102 | 100 |
| 1 | 112 | 109 | 106 | 104 | 110 | 107 | 104 | 102 | 103 | 101 | 99 | | 99 | 97 | 96 | | 96 | 94 | 93 | 91 |
| 2 | 105 | 100 | 95 | 91 | 103 | 98 | 93 | 90 | 94 | 91 | 88 | | 91 | 88 | 86 | | 89 | 86 | 84 | 82 |
| 3 | 99 | 91 | 85 | 80 | 96 | 89 | 84 | 79 | 87 | 82 | 78 | | 84 | 80 | 77 | | 82 | 78 | 76 | 74 |
| 4 | 92 | 83 | 76 | 71 | 90 | 82 | 76 | 71 | 79 | 74 | 70 | | 77 | 73 | 69 | | 75 | 71 | 68 | 66 |
| 5 | 86 | 76 | 69 | 64 | 84 | 75 | 68 | 63 | 73 | 67 | 63 | | 71 | 66 | 62 | | 70 | 65 | 62 | 60 |
| 6 | 80 | 70 | 63 | 57 | 79 | 69 | 62 | 57 | 67 | 61 | 57 | | 66 | 60 | 56 | | 64 | 60 | 56 | 54 |
| 7 | 75 | 64 | 57 | 52 | 74 | 63 | 57 | 52 | 62 | 56 | 51 | | 61 | 55 | 51 | | 60 | 55 | 51 | 49 |
| 8 | 71 | 59 | 52 | 47 | 69 | 59 | 52 | 47 | 57 | 51 | 47 | | 56 | 51 | 47 | | 55 | 50 | 46 | 45 |
| 9 | 66 | 55 | 48 | 43 | 65 | 54 | 48 | 43 | 53 | 47 | 43 | | 52 | 47 | 43 | | 51 | 46 | 43 | 41 |
| 10 | 63 | 51 | 44 | 40 | 61 | 51 | 44 | 40 | 50 | 44 | 39 | | 49 | 43 | 39 | | 48 | 43 | 39 | 38 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 14743 |
| 5° | 14799 |
| 10° | 14983 |
| 15° | 15276 |
| 20° | 15495 |
| 25° | 15559 |
| 30° | 15083 |
| 35° | 13766 |
| 40° | 11907 |
| 45° | 9376 |
| 50° | 6045 |
| 55° | 2968 |
| 60° | 1221 |
| 65° | 533 |
| 70° | 153 |
| 75° | 60 |
| 80° | 36 |
| 85° | 0 |



TEST NUMBER: P245370

CATALOG NUMBER: LD8B10D010 ER8B109727 8LBS0WH

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 45.7 | 5.4 |
| 10°-20° | 135.2 | 16.0 |
| 20°-30° | 209.4 | 24.8 |
| 30°-40° | 226.8 | 26.9 |
| 40°-50° | 163.2 | 19.3 |
| 50°-60° | 54.6 | 6.5 |
| 60°-70° | 8.3 | 1.0 |
| 70°-80° | 0.7 | 0.1 |
| 80°-90° | 0.1 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 390.3 | 46.2 |
| 0°-40° | 617.1 | 73.1 |
| 0°-60° | 834.9 | 98.9 |
| 0°-90° | 844.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 844.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 478 | |
| 5° | 478 | 46 |
| 15° | 478 | 135 |
| 25° | 457 | 209 |
| 35° | 366 | 227 |
| 45° | 215 | 163 |
| 55° | 55 | 55 |
| 65° | 7 | 8 |
| 75° | 0 | 1 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P245370

CATALOG NUMBER: LD8B10D010 ER8B109727 8LBS0WH

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|-------|
| 0° | 478.1 |
| 2.5° | 478.1 |
| 5° | 478.1 |
| 7.5° | 478.3 |
| 10° | 478.5 |
| 12.5° | 479.0 |
| 15° | 478.5 |
| 17.5° | 476.6 |
| 20° | 472.2 |
| 22.5° | 465.6 |
| 25° | 457.3 |
| 27.5° | 444.1 |
| 30° | 423.6 |
| 32.5° | 396.7 |
| 35° | 365.7 |
| 37.5° | 332.2 |
| 40° | 295.8 |
| 42.5° | 256.7 |
| 45° | 215.0 |
| 47.5° | 169.8 |
| 50° | 126.0 |
| 52.5° | 86.5 |
| 55° | 55.2 |
| 57.5° | 33.0 |
| 60° | 19.8 |
| 62.5° | 12.0 |
| 65° | 7.3 |
| 67.5° | 3.7 |
| 70° | 1.7 |
| 72.5° | 0.7 |
| 75° | 0.5 |
| 77.5° | 0.5 |
| 80° | 0.2 |
| 82.5° | 0.2 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)