

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250095

Luminaire Tested: **LD8B120D010 ER8B120940 8LBNOWH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250095  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13946)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B120D010 ER8B120940 8LBN0WH  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
90 CRI 4000 CCT WITH WHEAT TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10204.0 lumens  
Efficiency: N/A  
Efficacy: 86.3 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.66  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 118.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250095

CATALOG NUMBER: LD8B120D010 ER8B120940 8LBN0WH

### Luminous Intensity Polar Plot





TEST NUMBER: P250095

CATALOG NUMBER: LD8B120D010 ER8B120940 8LBNOWH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89
3	105	99	94	91	103	97	93	90	95	91	89	92	90	87	90	88	86	85
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76
6	92	84	79	75	90	83	78	74	82	77	74	80	76	74	79	76	73	72
7	88	80	74	71	87	79	74	70	78	73	70	77	73	70	76	72	69	68
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	72	69	66	65
9	81	72	67	64	80	72	67	64	71	66	63	70	66	63	69	66	63	62
10	78	69	64	61	77	69	64	61	68	63	60	67	63	60	67	63	60	59

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	632530
5°	611690
10°	520205
15°	397043
20°	303440
25°	235141
30°	160376
35°	94223
40°	28810
45°	11334
50°	173
55°	194
60°	222
65°	518
70°	965
75°	846
80°	639
85°	3786



TEST NUMBER: P250095

CATALOG NUMBER: LD8B120D010 ER8B120940 8LBNOWH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1791.5	17.6
10°-20°	3471.5	34.0
20°-30°	3125.4	30.6
30°-40°	1546.3	15.2
40°-50°	235.2	2.3
50°-60°	9.7	0.1
60°-70°	12.4	0.1
70°-80°	4.7	0.0
80°-90°	7.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	8388.4	82.2
0°-40°	9934.7	97.4
0°-60°	10179.6	99.8
0°-90°	10204.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	10204.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	20512	
5°	19761	###
15°	12437	3471
25°	6911	3125
35°	2503	1546
45°	260	235
55°	4	10
65°	7	12
75°	7	5
85°	11	7
90°	0	



TEST NUMBER: P250095

CATALOG NUMBER: LD8B120D010 ER8B120940 8LBNOWH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	20512.5
1°	20469.8
2°	20480.4
3°	20377.1
4°	20188.5
5°	19761.2
6°	19433.6
7°	18913.9
8°	18216.0
9°	17489.5
10°	16613.6
11°	15830.3
12°	14990.1
13°	14060.7
14°	13259.6
15°	12437.1
16°	11735.6
17°	11116.1
18°	10354.1
19°	9795.1
20°	9246.9
21°	8677.1
22°	8260.5
23°	7776.3
24°	7331.2
25°	6911.0
26°	6416.1
27°	5971.1
28°	5572.3
29°	5134.3
30°	4504.1
31°	4148.1
32°	3699.4
33°	3208.0
34°	2834.2
35°	2503.0
37.5°	1584.4
40°	715.7
42.5°	487.8
45°	259.9
47.5°	145.9
50°	3.6
52.5°	14.3
55°	3.6
57.5°	21.4



TEST NUMBER: P250095

CATALOG NUMBER: LD8B120D010 ER8B120940 8LBNOWH

**CANDELA DISTRIBUTION (continued):**

	0°
60°	3.6
62.5°	17.9
65°	7.1
67.5°	17.9
70°	10.7
72.5°	3.6
75°	7.1
77.5°	0.0
80°	3.6
82.5°	14.3
85°	10.7
87.5°	0.0
90°	0.0

(END OF REPORT)