

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244440

Luminaire Tested: **LD8B10D010 ER8B109730 8LBM0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244440
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27951)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B109730 8LBM0H
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 817.0 lumens
Efficiency: N/A
Efficacy: 80.1 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244440

CATALOG NUMBER: LD8B10D010 ER8B109730 8LBM0H

Luminous Intensity Polar Plot





TEST NUMBER: P244440

CATALOG NUMBER: LD8B10D010 ER8B109730 8LBM0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	95	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	82		86	83	80	79
4	96	88	82	77	94	86	81	77	84	80	76		82	78	75		80	77	74	73
5	90	82	75	71	89	81	75	70	79	74	70		77	73	69		75	72	69	67
6	85	76	70	65	84	75	69	65	74	68	64		72	68	64		71	67	64	62
7	81	71	65	60	80	70	64	60	69	64	60		68	63	59		67	62	59	58
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63	58	55	54
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		59	55	51	50
10	69	59	53	49	68	58	53	49	58	52	48		57	52	48		56	51	48	47

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P244440

CATALOG NUMBER: LD8B10D010 ER8B109730 8LBM0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.4	9.2
10°-20°	189.8	23.2
20°-30°	253.2	31.0
30°-40°	195.2	23.9
40°-50°	72.8	8.9
50°-60°	23.8	2.9
60°-70°	5.5	0.7
70°-80°	1.1	0.1
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	518.5	63.5
0°-40°	713.7	87.3
0°-60°	810.3	99.2
0°-90°	817.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	817.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	856	
5°	817	75
15°	675	190
25°	558	253
35°	318	195
45°	88	73
55°	25	24
65°	5	5
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P244440

CATALOG NUMBER: LD8B10D010 ER8B109730 8LBM0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	856.1
1°	852.4
2°	846.2
3°	838.1
4°	828.4
5°	816.7
6°	803.4
7°	788.2
8°	772.0
9°	755.2
10°	739.8
11°	724.9
12°	711.1
13°	698.4
14°	686.7
15°	675.2
16°	663.5
17°	652.1
18°	640.4
19°	628.9
20°	617.8
21°	606.3
22°	595.1
23°	583.4
24°	571.1
25°	557.5
26°	542.4
27°	525.8
28°	507.5
29°	487.0
30°	464.6
32.5°	398.8
35°	317.6
37.5°	235.2
40°	166.5
42.5°	119.3
45°	88.4
47.5°	66.6
50°	49.2
52.5°	35.1
55°	25.0
57.5°	17.2
60°	11.3
62.5°	7.4
65°	4.9



TEST NUMBER: P244440

CATALOG NUMBER: LD8B10D010 ER8B109730 8LBM0H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	3.3
70°	2.1
72.5°	1.4
75°	1.0
77.5°	0.6
80°	0.4
82.5°	0.2
85°	0.2
87.5°	0.0
90°	0.0

(END OF REPORT)