

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244296

Luminaire Tested: **LD8B10D010 ER8B109730 8LBW0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244296
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27940)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B10D010 ER8B109730 8LBW0H
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 835.0 lumens
Efficiency: N/A
Efficacy: 81.9 lumens/watt
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.12
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 10.2
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244296

CATALOG NUMBER: LD8B10D010 ER8B109730 8LBW0H

Luminous Intensity Polar Plot





TEST NUMBER: P244296

CATALOG NUMBER: LD8B10D010 ER8B109730 8LBW0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	109	107	104	110	107	105	102	103	101	99		99	98	96		96	95	93	92
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89	87	85	83
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83	79	77	75
4	93	84	78	73	91	83	77	72	81	75	71		79	74	71		77	73	70	68
5	87	77	71	66	85	76	70	65	75	69	65		73	68	64		71	67	63	62
6	82	71	65	60	80	71	64	59	69	63	59		68	62	58		66	62	58	56
7	77	66	59	54	75	65	59	54	64	58	54		63	57	53		62	57	53	52
8	72	61	54	50	71	61	54	50	60	54	49		58	53	49		57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46		55	49	45		54	49	45	44
10	64	53	47	42	63	53	47	42	52	46	42		51	46	42		50	45	42	40

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P244296

CATALOG NUMBER: LD8B10D010 ER8B109730 8LBW0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.8	6.3
10°-20°	151.4	18.1
20°-30°	227.8	27.3
30°-40°	225.6	27.0
40°-50°	114.6	13.7
50°-60°	46.2	5.5
60°-70°	14.0	1.7
70°-80°	2.4	0.3
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	432.0	51.7
0°-40°	657.5	78.7
0°-60°	818.3	98.0
0°-90°	835.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	835.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	560	
5°	556	53
15°	537	151
25°	498	228
35°	371	226
45°	140	115
55°	50	46
65°	13	14
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P244296

CATALOG NUMBER: LD8B10D010 ER8B109730 8LBW0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	559.9
1°	558.7
2°	557.7
3°	557.5
4°	557.2
5°	556.5
6°	555.6
7°	553.6
8°	550.7
9°	548.1
10°	545.2
11°	542.8
12°	541.1
13°	539.9
14°	538.4
15°	536.7
16°	534.6
17°	531.9
18°	528.8
19°	525.1
20°	521.0
21°	516.7
22°	512.4
23°	507.8
24°	502.9
25°	497.6
26°	491.8
27°	484.4
28°	475.7
29°	465.3
30°	453.2
32.5°	418.0
35°	371.2
37.5°	312.8
40°	247.6
42.5°	187.0
45°	140.5
47.5°	107.4
50°	84.2
52.5°	65.4
55°	49.7
57.5°	36.9
60°	27.8
62.5°	19.8
65°	12.8



TEST NUMBER: P244296

CATALOG NUMBER: LD8B10D010 ER8B109730 8LBW0H

CANDELA DISTRIBUTION (continued):

	0°
67.5°	8.0
70°	5.1
72.5°	3.1
75°	1.9
77.5°	1.2
80°	0.7
82.5°	0.5
85°	0.2
87.5°	0.0
90°	0.0

(END OF REPORT)