

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P249793

Luminaire Tested: **LD8B100D010 ER8B100830 8LBN0H**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P249793  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13959)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B100D010 ER8B100830 8LBN0H  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9420.0 lumens  
Efficiency: N/A  
Efficacy: 88.6 lumens/watt  
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.81  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 106.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P249793

CATALOG NUMBER: LD8B100D010 ER8B100830 8LBN0H

### Luminous Intensity Polar Plot





TEST NUMBER: P249793

CATALOG NUMBER: LD8B100D010 ER8B100830 8LBNOH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	85	83	82
4	98	91	85	81	96	89	84	81	87	83	80		85	82	79		83	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74		81	77	74		79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	68	67
7	84	75	70	66	83	75	69	65	74	69	65		72	68	65		71	67	64	63
8	81	71	65	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64	60	57	56
10	73	64	58	55	72	64	58	55	63	58	54		62	57	54		61	57	54	53

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	398408
5°	393516
10°	363432
15°	316904
20°	271458
25°	227227
30°	172871
35°	107162
40°	52870
45°	25162
50°	12233
55°	6000
60°	3737
65°	2561
70°	1434
75°	1144
80°	1137
85°	1132



TEST NUMBER: P249793

CATALOG NUMBER: LD8B100D010 ER8B100830 8LBNOH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1178.2	12.5
10°-20°	2766.0	29.4
20°-30°	3023.1	32.1
30°-40°	1799.0	19.1
40°-50°	493.5	5.2
50°-60°	111.8	1.2
60°-70°	34.5	0.4
70°-80°	10.5	0.1
80°-90°	3.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6967.2	74.0
0°-40°	8766.2	93.1
0°-60°	9371.5	99.5
0°-90°	9420.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9420.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	12920	
5°	12713	###
15°	9927	2766
25°	6678	3023
35°	2847	1799
45°	577	493
55°	112	112
65°	35	35
75°	10	11
85°	3	3
90°	0	



TEST NUMBER: P249793

CATALOG NUMBER: LD8B100D010 ER8B100830 8LBNOH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	12920.1
1°	12945.6
2°	12929.7
3°	12897.8
4°	12824.5
5°	12712.9
6°	12569.5
7°	12378.2
8°	12155.1
9°	11896.9
10°	11606.8
11°	11297.6
12°	10966.0
13°	10624.9
14°	10271.1
15°	9926.8
16°	9588.9
17°	9257.4
18°	8925.8
19°	8594.3
20°	8272.3
22.5°	7462.6
25°	6678.4
27.5°	5814.5
30°	4855.0
32.5°	3825.4
35°	2846.7
37.5°	1979.6
40°	1313.4
42.5°	860.7
45°	577.0
47.5°	382.5
50°	255.0
52.5°	156.2
55°	111.6
57.5°	79.7
60°	60.6
62.5°	44.6
65°	35.1
67.5°	22.3
70°	15.9
72.5°	12.8
75°	9.6
77.5°	6.4
80°	6.4



TEST NUMBER: P249793

CATALOG NUMBER: LD8B100D010 ER8B100830 8LBNOH

**CANDELA DISTRIBUTION (continued):**

	0°
82.5°	3.2
85°	3.2
87.5°	3.2
90°	0.0

(END OF REPORT)