

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250452

Luminaire Tested: **LD8B120D010 ER8B1209730 8LBN0B**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P250452  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13948)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B120D010 ER8B1209730 8LBN0B  
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
97 CRI 3000 CCT WITH SPECULAR BLACK TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5364.0 lumens  
Efficiency: N/A  
Efficacy: 45.3 lumens/watt  
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 118.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P250452

CATALOG NUMBER: LD8B120D010 ER8B1209730 8LBN0B

### Luminous Intensity Polar Plot





TEST NUMBER: P250452

CATALOG NUMBER: LD8B120D010 ER8B1209730 8LBN0B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102		101	100	99		98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72		79	75	71		77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74	70	67	66
8	83	74	68	64	81	73	68	64	72	67	64		71	67	64		70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61		68	63	60		67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57		65	60	57		64	60	57	56

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P250452

CATALOG NUMBER: LD8B120D010 ER8B1209730 8LBN0B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	769.4	14.3
10°-20°	1672.3	31.2
20°-30°	1795.4	33.5
30°-40°	970.3	18.1
40°-50°	151.4	2.8
50°-60°	4.1	0.1
60°-70°	1.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4237.1	79.0
0°-40°	5207.4	97.1
0°-60°	5363.0	100.0
0°-90°	5364.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5364.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	8571	
5°	8402	769
15°	5971	1672
25°	3980	1795
35°	1524	970
45°	140	151
55°	0	4
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P250452

CATALOG NUMBER: LD8B120D010 ER8B1209730 8LBN0B

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	8571.1
1°	8587.4
2°	8579.3
3°	8550.0
4°	8493.5
5°	8402.1
6°	8276.2
7°	8106.9
8°	7895.0
9°	7651.0
10°	7379.7
11°	7095.2
12°	6800.0
13°	6505.1
14°	6231.1
15°	5970.9
16°	5732.0
17°	5501.2
18°	5286.5
19°	5085.5
20°	4892.1
21°	4704.2
22°	4527.0
23°	4350.1
24°	4165.0
25°	3979.7
26°	3791.8
27°	3577.2
28°	3340.9
29°	3099.7
30°	2847.3
31°	2576.3
32°	2305.0
33°	2036.8
34°	1765.8
35°	1524.2
37.5°	974.1
40°	563.6
42.5°	300.7
45°	139.7
47.5°	75.3
50°	24.3
52.5°	2.7
55°	0.0
57.5°	2.7



TEST NUMBER: P250452

CATALOG NUMBER: LD8B120D010 ER8B1209730 8LBN0B

**CANDELA DISTRIBUTION (continued):**

	0°
60°	2.7
62.5°	0.0
65°	0.0
67.5°	2.7
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)