

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250032

Luminaire Tested: **LD8B120D010 ER8B1209730 8LBN0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250032
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13951)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B120D010 ER8B1209730 8LBN0WMH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8002.0 lumens
Efficiency: N/A
Efficacy: 67.6 lumens/watt
Spacing Criteria (0/90/45): 0.74 / 0.74 / 0.79
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 118.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250032

CATALOG NUMBER: LD8B120D010 ER8B1209730 8LBN0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P250032

CATALOG NUMBER: LD8B120D010 ER8B1209730 8LBN0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94
2	108	104	100	97	106	102	99	96	99	96	93	96	94	91	93	91	90	88
3	103	97	92	89	101	96	91	88	93	89	86	91	88	85	89	86	84	82
4	98	91	86	82	97	90	85	81	88	84	80	86	82	79	84	81	79	77
5	94	86	80	76	92	85	80	76	83	78	75	81	77	74	80	76	74	72
6	89	81	75	71	88	80	75	71	79	74	70	77	73	70	76	72	69	68
7	85	76	71	67	84	76	70	66	74	70	66	73	69	66	72	68	65	64
8	81	72	66	63	80	72	66	62	71	66	62	70	65	62	69	65	62	60
9	78	68	63	59	77	68	63	59	67	62	59	66	62	58	65	61	58	57
10	74	65	59	56	73	65	59	56	64	59	56	63	59	55	62	58	55	54

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P250032

CATALOG NUMBER: LD8B120D010 ER8B1209730 8LBN0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1057.8	13.2
10°-20°	2427.1	30.3
20°-30°	2578.5	32.2
30°-40°	1471.1	18.4
40°-50°	364.8	4.6
50°-60°	71.7	0.9
60°-70°	21.7	0.3
70°-80°	5.1	0.1
80°-90°	4.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6063.4	75.8
0°-40°	7534.5	94.2
0°-60°	7971.0	99.6
0°-90°	8002.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8002.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11655	
5°	11449	###
15°	8720	2427
25°	5692	2578
35°	2300	1471
45°	412	365
55°	67	72
65°	17	22
75°	0	5
85°	6	4
90°	0	



TEST NUMBER: P250032

CATALOG NUMBER: LD8B120D010 ER8B1209730 8LBN0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	11655.1
1°	11677.4
2°	11669.1
3°	11627.3
4°	11554.9
5°	11449.0
6°	11309.9
7°	11117.6
8°	10897.6
9°	10638.7
10°	10354.5
11°	10053.8
12°	9730.7
13°	9402.1
14°	9065.1
15°	8719.7
16°	8393.9
17°	8065.3
18°	7756.1
19°	7441.5
20°	7143.5
22.5°	6405.4
25°	5692.4
27.5°	4926.7
30°	4080.0
32.5°	3172.0
35°	2300.4
37.5°	1584.6
40°	1024.9
42.5°	649.0
45°	412.2
47.5°	270.2
50°	169.9
52.5°	103.1
55°	66.8
57.5°	52.9
60°	33.4
62.5°	30.6
65°	16.8
67.5°	16.8
70°	14.0
72.5°	8.4
75°	0.0
77.5°	2.8
80°	2.8



TEST NUMBER: P250032

CATALOG NUMBER: LD8B120D010 ER8B1209730 8LBN0WMH

CANDELA DISTRIBUTION (continued):

	0°
82.5°	5.6
85°	5.6
87.5°	2.8
90°	0.0

(END OF REPORT)