

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246469

Luminaire Tested: **LD8B15D010 ER8B15830 8LBS0B**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246469
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-17)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B15D010 ER8B15830 8LBS0B
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3000 CCT WITH SPECULAR BLACK TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1359.0 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.25
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246469

CATALOG NUMBER: LD8B15D010 ER8B15830 8LBS0B

Luminous Intensity Polar Plot





TEST NUMBER: P246469

CATALOG NUMBER: LD8B15D010 ER8B15830 8LBSOB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |
| 1 | 112 | 109 | 106 | 103 | 110 | 107 | 104 | 102 | 103 | 101 | 99 | 99 | 97 | 96 | 96 | 94 | 93 | 91 |
| 2 | 105 | 99 | 94 | 90 | 103 | 98 | 93 | 89 | 94 | 90 | 87 | 91 | 88 | 85 | 88 | 86 | 84 | 82 |
| 3 | 98 | 90 | 84 | 79 | 96 | 89 | 83 | 79 | 86 | 81 | 77 | 84 | 80 | 76 | 81 | 78 | 75 | 73 |
| 4 | 92 | 82 | 76 | 70 | 90 | 81 | 75 | 70 | 79 | 73 | 69 | 77 | 72 | 68 | 75 | 71 | 67 | 66 |
| 5 | 86 | 75 | 68 | 63 | 84 | 74 | 68 | 63 | 72 | 66 | 62 | 71 | 65 | 61 | 69 | 64 | 61 | 59 |
| 6 | 80 | 69 | 62 | 56 | 78 | 68 | 61 | 56 | 67 | 60 | 56 | 65 | 60 | 55 | 64 | 59 | 55 | 53 |
| 7 | 75 | 63 | 56 | 51 | 73 | 63 | 56 | 51 | 61 | 55 | 51 | 60 | 54 | 50 | 59 | 54 | 50 | 48 |
| 8 | 70 | 59 | 51 | 46 | 69 | 58 | 51 | 46 | 57 | 50 | 46 | 56 | 50 | 46 | 54 | 49 | 46 | 44 |
| 9 | 66 | 54 | 47 | 42 | 65 | 54 | 47 | 42 | 53 | 46 | 42 | 52 | 46 | 42 | 51 | 45 | 42 | 40 |
| 10 | 62 | 50 | 43 | 39 | 61 | 50 | 43 | 39 | 49 | 43 | 39 | 48 | 42 | 38 | 47 | 42 | 38 | 37 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 24277 |
| 5° | 24249 |
| 10° | 24123 |
| 15° | 23946 |
| 20° | 23683 |
| 25° | 23310 |
| 30° | 22625 |
| 35° | 21559 |
| 40° | 19970 |
| 45° | 16755 |
| 50° | 11077 |
| 55° | 5468 |
| 60° | 2171 |
| 65° | 846 |
| 70° | 126 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |



TEST NUMBER: P246469

CATALOG NUMBER: LD8B15D010 ER8B15830 8LBSOB

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 74.3 | 5.5 |
| 10°-20° | 211.4 | 15.6 |
| 20°-30° | 314.7 | 23.2 |
| 30°-40° | 356.5 | 26.2 |
| 40°-50° | 288.2 | 21.2 |
| 50°-60° | 100.0 | 7.4 |
| 60°-70° | 13.7 | 1.0 |
| 70°-80° | 0.2 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 600.5 | 44.2 |
| 0°-40° | 957.0 | 70.4 |
| 0°-60° | 1345.1 | 99.0 |
| 0°-90° | 1359.0 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1359.0 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-----|------|
| 0° | 787 | |
| 5° | 783 | 74 |
| 15° | 750 | 211 |
| 25° | 685 | 315 |
| 35° | 573 | 356 |
| 45° | 384 | 288 |
| 55° | 102 | 100 |
| 65° | 12 | 14 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P246469

CATALOG NUMBER: LD8B15D010 ER8B15830 8LBS0B

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|-------|
| 0° | 787.3 |
| 2.5° | 786.3 |
| 5° | 783.4 |
| 7.5° | 777.6 |
| 10° | 770.4 |
| 12.5° | 760.8 |
| 15° | 750.1 |
| 17.5° | 736.6 |
| 20° | 721.7 |
| 22.5° | 704.3 |
| 25° | 685.1 |
| 27.5° | 661.9 |
| 30° | 635.4 |
| 32.5° | 605.5 |
| 35° | 572.7 |
| 37.5° | 536.6 |
| 40° | 496.1 |
| 42.5° | 446.4 |
| 45° | 384.2 |
| 47.5° | 309.0 |
| 50° | 230.9 |
| 52.5° | 158.1 |
| 55° | 101.7 |
| 57.5° | 60.3 |
| 60° | 35.2 |
| 62.5° | 20.7 |
| 65° | 11.6 |
| 67.5° | 5.3 |
| 70° | 1.4 |
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

(END OF REPORT)