

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244669

Luminaire Tested: **LD8B15D010 ER8B15830 8LBW0WMH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244669
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-44)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B15D010 ER8B15830 8LBW0WMH
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 3000 CCT WITH WARM HAZE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1436.0 lumens
Efficiency: N/A
Efficacy: 99.7 lumens/watt
Spacing Criteria (0/90/45): 1.14 / 1.14 / 1.06
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244669

CATALOG NUMBER: LD8B15D010 ER8B15830 8LBW0WMH

Luminous Intensity Polar Plot





TEST NUMBER: P244669

CATALOG NUMBER: LD8B15D010 ER8B15830 8LBW0WMH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	83
3	99	91	86	81	97	90	85	80	87	83	79	85	81	78	82	79	76	75
4	93	84	77	72	91	83	77	72	80	75	71	78	74	70	76	73	69	68
5	87	77	70	65	85	76	70	65	74	69	64	73	68	64	71	67	63	62
6	82	71	64	59	80	70	64	59	69	63	59	67	62	58	66	61	58	56
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51
8	72	61	54	50	71	61	54	50	60	54	49	58	53	49	57	53	49	47
9	68	57	50	46	67	57	50	46	56	50	46	55	49	45	54	49	45	44
10	65	54	47	42	63	53	47	42	52	46	42	51	46	42	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	32091
5°	31446
10°	30448
15°	30041
20°	29859
25°	29482
30°	27898
35°	23008
40°	14367
45°	9241
50°	7162
55°	5516
60°	4181
65°	2714
70°	1163
75°	572
80°	249
85°	177



TEST NUMBER: P244669

CATALOG NUMBER: LD8B15D010 ER8B15830 8LBW0WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	95.5	6.7
10°-20°	265.8	18.5
20°-30°	396.0	27.6
30°-40°	367.7	25.6
40°-50°	173.7	12.1
50°-60°	93.3	6.5
60°-70°	37.5	2.6
70°-80°	5.9	0.4
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	757.3	52.7
0°-40°	1125.1	78.3
0°-60°	1392.1	96.9
0°-90°	1436.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1436.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1041	
5°	1016	96
15°	941	266
25°	866	396
35°	611	368
45°	212	174
55°	103	93
65°	37	37
75°	5	6
85°	0	1
90°	0	



TEST NUMBER: P244669

CATALOG NUMBER: LD8B15D010 ER8B15830 8LBW0WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1040.7
2.5°	1033.5
5°	1015.9
7.5°	993.4
10°	972.4
12.5°	955.3
15°	941.0
17.5°	926.2
20°	909.9
22.5°	891.3
25°	866.5
27.5°	831.7
30°	783.5
32.5°	712.9
35°	611.2
37.5°	481.5
40°	356.9
42.5°	265.8
45°	211.9
47.5°	177.0
50°	149.3
52.5°	124.5
55°	102.6
57.5°	83.5
60°	67.8
62.5°	53.0
65°	37.2
67.5°	21.9
70°	12.9
72.5°	7.6
75°	4.8
77.5°	2.9
80°	1.4
82.5°	1.0
85°	0.5
87.5°	0.0
90°	0.0

(END OF REPORT)