

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P249856

Luminaire Tested: **LD8B100D010 ER8B100927 8LBN0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P249856
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13959)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B100D010 ER8B100927 8LBNOH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7673.6 lumens
Efficiency: N/A
Efficacy: 72.2 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.81
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 106.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P249856

CATALOG NUMBER: LD8B100D010 ER8B100927 8LBN0H

Luminous Intensity Polar Plot





TEST NUMBER: P249856

CATALOG NUMBER: LD8B100D010 ER8B100927 8LBNOH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101		101	100	98		98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93		96	93	91		93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86		90	87	85		88	85	83	82
4	98	91	85	81	96	89	84	81	87	83	80		85	82	79		83	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74		81	77	74		79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69		76	72	69		75	71	68	67
7	84	75	70	66	83	75	69	65	74	69	65		72	68	65		71	67	64	63
8	81	71	65	62	79	71	65	61	70	65	61		69	64	61		68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58		65	61	57		64	60	57	56
10	73	64	58	55	72	64	58	55	63	58	54		62	57	54		61	57	54	53

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P249856

CATALOG NUMBER: LD8B100D010 ER8B100927 8LBNOH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	959.7	12.5
10°-20°	2253.2	29.4
20°-30°	2462.7	32.1
30°-40°	1465.5	19.1
40°-50°	402.0	5.2
50°-60°	91.1	1.2
60°-70°	28.1	0.4
70°-80°	8.5	0.1
80°-90°	2.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5675.6	74.0
0°-40°	7141.1	93.1
0°-60°	7634.1	99.5
0°-90°	7673.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7673.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10525	
5°	10356	960
15°	8086	2253
25°	5440	2463
35°	2319	1465
45°	470	402
55°	91	91
65°	29	28
75°	8	9
85°	3	3
90°	0	



TEST NUMBER: P249856

CATALOG NUMBER: LD8B100D010 ER8B100927 8LBNOH

CANDELA DISTRIBUTION (FULL):

	0°
0°	10524.8
1°	10545.6
2°	10532.7
3°	10506.7
4°	10447.0
5°	10356.1
6°	10239.2
7°	10083.4
8°	9901.7
9°	9691.3
10°	9454.9
11°	9203.1
12°	8933.1
13°	8655.2
14°	8367.0
15°	8086.5
16°	7811.2
17°	7541.1
18°	7271.1
19°	7001.0
20°	6738.8
22.5°	6079.2
25°	5440.3
27.5°	4736.6
30°	3954.9
32.5°	3116.1
35°	2319.0
37.5°	1612.6
40°	1069.9
42.5°	701.1
45°	470.0
47.5°	311.6
50°	207.8
52.5°	127.2
55°	90.9
57.5°	64.9
60°	49.4
62.5°	36.3
65°	28.6
67.5°	18.2
70°	12.9
72.5°	10.4
75°	7.8
77.5°	5.2
80°	5.2



TEST NUMBER: P249856

CATALOG NUMBER: LD8B100D010 ER8B100927 8LBN0H

CANDELA DISTRIBUTION (continued):

	0°
82.5°	2.6
85°	2.6
87.5°	2.6
90°	0.0

(END OF REPORT)