

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250367

Luminaire Tested: **LD8B100D010 ER8B100930 8LBN0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250367
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13948)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B100D010 ER8B100930 8LBN0GPH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7280.9 lumens
Efficiency: N/A
Efficacy: 68.5 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 106.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250367

CATALOG NUMBER: LD8B100D010 ER8B100930 8LBN0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P250367

CATALOG NUMBER: LD8B100D010 ER8B100930 8LBN0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102		101	100	99		98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72		79	75	71		77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74	70	67	66
8	83	74	68	64	81	73	68	64	72	67	64		71	67	64		70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61		68	63	60		67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57		65	60	57		64	60	57	56

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P250367

CATALOG NUMBER: LD8B100D010 ER8B100930 8LBN0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1044.4	14.3
10°-20°	2269.9	31.2
20°-30°	2436.9	33.5
30°-40°	1317.1	18.1
40°-50°	205.5	2.8
50°-60°	5.6	0.1
60°-70°	1.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5751.3	79.0
0°-40°	7068.4	97.1
0°-60°	7279.5	100.0
0°-90°	7280.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7280.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11634	
5°	11405	###
15°	8105	2270
25°	5402	2437
35°	2069	1317
45°	190	205
55°	0	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P250367

CATALOG NUMBER: LD8B100D010 ER8B100930 8LBNOGPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	11634.2
1°	11656.3
2°	11645.3
3°	11605.4
4°	11528.8
5°	11404.7
6°	11233.9
7°	11004.1
8°	10716.3
9°	10385.2
10°	10017.0
11°	9630.7
12°	9230.1
13°	8829.8
14°	8457.9
15°	8104.7
16°	7780.4
17°	7467.2
18°	7175.7
19°	6902.9
20°	6640.4
21°	6385.3
22°	6144.8
23°	5904.8
24°	5653.4
25°	5401.9
26°	5146.7
27°	4855.5
28°	4534.8
29°	4207.4
30°	3864.9
31°	3497.0
32°	3128.8
33°	2764.6
34°	2396.8
35°	2068.8
37.5°	1322.2
40°	765.0
42.5°	408.0
45°	189.6
47.5°	102.2
50°	33.1
52.5°	3.7
55°	0.0
57.5°	3.7



TEST NUMBER: P250367

CATALOG NUMBER: LD8B100D010 ER8B100930 8LBNOGPH

CANDELA DISTRIBUTION (continued):

	0°
60°	3.7
62.5°	0.0
65°	0.0
67.5°	3.7
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)