

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P243817

Luminaire Tested: **LD8B15D010 ER8B15840 8LBW0LI**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P243817  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27941)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B15D010 ER8B15840 8LBW0LI  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 4000 CCT WITH SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1616.0 lumens  
Efficiency: N/A  
Efficacy: 112.2 lumens/watt  
Spacing Criteria (0/90/45): 1.34 / 1.34 / 1.17  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P243817

CATALOG NUMBER: LD8B15D010 ER8B15840 8LBW0LI

### Luminous Intensity Polar Plot





TEST NUMBER: P243817

CATALOG NUMBER: LD8B15D010 ER8B15840 8LBW0LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54
8	74	63	56	52	72	62	56	52	61	55	51	60	55	51	59	54	51	49
9	70	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	28672
5°	29521
10°	31979
15°	34989
20°	36402
25°	36270
30°	34019
35°	28527
40°	19861
45°	11378
50°	6107
55°	2521
60°	629
65°	161
70°	81
75°	48
80°	71
85°	0



TEST NUMBER: P243817

CATALOG NUMBER: LD8B15D010 ER8B15840 8LBW0LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	93.2	5.8
10°-20°	308.9	19.1
20°-30°	486.1	30.1
30°-40°	462.3	28.6
40°-50°	213.2	13.2
50°-60°	48.4	3.0
60°-70°	3.2	0.2
70°-80°	0.6	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	888.2	55.0
0°-40°	1350.5	83.6
0°-60°	1612.1	99.8
0°-90°	1616.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1616.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	930	
5°	954	93
15°	1096	309
25°	1066	486
35°	758	462
45°	261	213
55°	47	48
65°	2	3
75°	0	1
85°	0	0
90°	0	



TEST NUMBER: P243817

CATALOG NUMBER: LD8B15D010 ER8B15840 8LBW0LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	929.8
1°	929.4
2°	931.1
3°	936.4
4°	944.4
5°	953.7
6°	965.2
7°	977.5
8°	990.4
9°	1005.4
10°	1021.3
11°	1037.2
12°	1054.0
13°	1070.0
14°	1084.5
15°	1096.0
16°	1104.4
17°	1110.2
18°	1112.8
19°	1112.4
20°	1109.3
21°	1104.0
22°	1097.4
23°	1088.5
24°	1078.4
25°	1066.0
26°	1051.4
27°	1032.8
28°	1010.7
29°	985.1
30°	955.4
32.5°	866.6
35°	757.8
37.5°	631.4
40°	493.4
42.5°	364.8
45°	260.9
47.5°	184.8
50°	127.3
52.5°	81.4
55°	46.9
57.5°	23.4
60°	10.2
62.5°	4.0
65°	2.2



TEST NUMBER: P243817

CATALOG NUMBER: LD8B15D010 ER8B15840 8LBW0LI

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	1.3
70°	0.9
72.5°	0.9
75°	0.4
77.5°	0.4
80°	0.4
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)