

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244903

Luminaire Tested: **LD8B15D010 ER8B15850 8LBS0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P244903  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-14)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B15D010 ER8B15850 8LBS0WMH  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 5000 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1663.0 lumens  
Efficiency: N/A  
Efficacy: 115.5 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P244903

CATALOG NUMBER: LD8B15D010 ER8B15850 8LBS0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P244903

CATALOG NUMBER: LD8B15D010 ER8B15850 8LBS0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	92	91
2	105	99	94	89	102	97	92	88	94	90	86	90	87	85	88	85	83	81
3	98	90	83	78	95	88	82	78	85	80	76	83	79	75	80	77	74	72
4	91	82	75	69	89	80	74	69	78	72	68	76	71	67	74	70	66	65
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58
6	79	68	61	55	77	67	60	55	66	59	55	64	58	54	63	58	54	52
7	74	63	55	50	72	62	55	50	60	54	49	59	53	49	58	53	49	47
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	54	48	45	43
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	29076
5°	28985
10°	28726
15°	28441
20°	28136
25°	27689
30°	26929
35°	25703
40°	23818
45°	20113
50°	13797
55°	7613
60°	3824
65°	2152
70°	1172
75°	834
80°	533
85°	354



TEST NUMBER: P244903

CATALOG NUMBER: LD8B15D010 ER8B15850 8LBS0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	88.8	5.3
10°-20°	251.3	15.1
20°-30°	374.1	22.5
30°-40°	424.9	25.6
40°-50°	347.3	20.9
50°-60°	136.1	8.2
60°-70°	31.7	1.9
70°-80°	7.6	0.5
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	714.1	42.9
0°-40°	1139.0	68.5
0°-60°	1622.4	97.6
0°-90°	1663.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1663.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	943	
5°	936	89
15°	891	251
25°	814	374
35°	683	425
45°	461	347
55°	142	136
65°	30	32
75°	7	8
85°	1	1
90°	0	



TEST NUMBER: P244903

CATALOG NUMBER: LD8B15D010 ER8B15850 8LBS0WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	942.9
2.5°	941.4
5°	936.4
7.5°	927.9
10°	917.4
12.5°	904.4
15°	890.9
17.5°	874.9
20°	857.4
22.5°	836.9
25°	813.8
27.5°	786.8
30°	756.3
32.5°	721.8
35°	682.8
37.5°	639.8
40°	591.7
42.5°	533.7
45°	461.2
47.5°	376.2
50°	287.6
52.5°	206.6
55°	141.6
57.5°	92.5
60°	62.0
62.5°	42.5
65°	29.5
67.5°	19.5
70°	13.0
72.5°	9.0
75°	7.0
77.5°	5.0
80°	3.0
82.5°	1.5
85°	1.0
87.5°	0.5
90°	0.0

(END OF REPORT)