

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246559

Luminaire Tested: **LD8B15D010 ER8B15850 8LBW0MW**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P246559  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-48)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B15D010 ER8B15850 8LBW0MW  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 5000 CCT WITH MATTE WHITE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1586.0 lumens  
Efficiency: N/A  
Efficacy: 110.1 lumens/watt  
Spacing Criteria (0/90/45): 1.11 / 1.11 / 1.05  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P246559

CATALOG NUMBER: LD8B15D010 ER8B15850 8LBW0MW

### Luminous Intensity Polar Plot





TEST NUMBER: P246559

CATALOG NUMBER: LD8B15D010 ER8B15850 8LBW0MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96		97	95	93		94	92	91	89
2	103	97	91	87	101	95	90	86	92	87	84		88	85	82		86	83	80	78
3	96	88	81	76	94	86	80	75	83	78	74		81	76	73		78	75	72	70
4	90	80	73	67	88	79	72	67	76	70	66		74	69	65		72	68	64	62
5	84	73	66	60	82	72	65	60	70	64	59		68	63	59		67	62	58	56
6	79	67	60	54	77	66	59	54	65	58	54		63	58	53		62	57	53	51
7	74	62	55	49	72	61	54	49	60	54	49		59	53	49		57	52	48	47
8	69	58	50	45	68	57	50	45	56	50	45		55	49	45		54	48	45	43
9	65	54	47	42	64	53	46	42	52	46	41		51	45	41		50	45	41	40
10	62	50	43	39	61	50	43	39	49	43	38		48	42	38		47	42	38	37

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	32403
5°	31858
10°	30855
15°	30143
20°	29714
25°	29131
30°	27350
35°	22327
40°	13831
45°	9367
50°	8251
55°	7790
60°	7728
65°	7486
70°	6708
75°	5814
80°	4919
85°	3927



TEST NUMBER: P246559

CATALOG NUMBER: LD8B15D010 ER8B15850 8LBW0MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	96.8	6.1
10°-20°	266.7	16.8
20°-30°	391.1	24.7
30°-40°	357.5	22.5
40°-50°	177.0	11.2
50°-60°	130.9	8.3
60°-70°	100.6	6.3
70°-80°	52.4	3.3
80°-90°	13.1	0.8
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	754.6	47.6
0°-40°	1112.1	70.1
0°-60°	1419.9	89.5
0°-90°	1586.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1586.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1051	
5°	1029	97
15°	944	267
25°	856	391
35°	593	357
45°	215	177
55°	145	131
65°	103	101
75°	49	52
85°	11	13
90°	0	



TEST NUMBER: P246559

CATALOG NUMBER: LD8B15D010 ER8B15850 8LBW0MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1050.8
2.5°	1045.3
5°	1029.2
7.5°	1007.6
10°	985.4
12.5°	963.8
15°	944.2
17.5°	925.6
20°	905.5
22.5°	882.8
25°	856.2
27.5°	819.4
30°	768.1
32.5°	696.2
35°	593.1
37.5°	465.3
40°	343.6
42.5°	260.1
45°	214.8
47.5°	190.1
50°	172.0
52.5°	157.4
55°	144.9
57.5°	134.3
60°	125.3
62.5°	115.7
65°	102.6
67.5°	88.5
70°	74.4
72.5°	61.4
75°	48.8
77.5°	37.7
80°	27.7
82.5°	19.1
85°	11.1
87.5°	4.0
90°	0.0

(END OF REPORT)