

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246739

Luminaire Tested: **LD8B15D010 ER8B15927 8LBM0MW**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P246739
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201674)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B15D010 ER8B15927 8LBM0MW
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH MATTE WHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1200.3 lumens
Efficiency: N/A
Efficacy: 83.4 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.93
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P246739

CATALOG NUMBER: LD8B15D010 ER8B15927 8LBM0MW

Luminous Intensity Polar Plot





TEST NUMBER: P246739

CATALOG NUMBER: LD8B15D010 ER8B15927 8LBM0MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | | 50 | 30 | 10 | | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | | 106 | 106 | 106 | | 102 | 102 | 102 | 100 |
| 1 | 112 | 108 | 105 | 102 | 109 | 106 | 103 | 100 | 102 | 99 | 97 | | 98 | 96 | 94 | | 94 | 93 | 91 | 89 |
| 2 | 104 | 98 | 93 | 88 | 102 | 96 | 91 | 87 | 93 | 89 | 85 | | 90 | 86 | 83 | | 87 | 84 | 82 | 80 |
| 3 | 97 | 89 | 83 | 78 | 95 | 88 | 82 | 77 | 85 | 80 | 76 | | 82 | 78 | 75 | | 80 | 76 | 73 | 71 |
| 4 | 91 | 82 | 75 | 69 | 89 | 80 | 74 | 69 | 78 | 72 | 68 | | 76 | 71 | 67 | | 74 | 70 | 66 | 65 |
| 5 | 85 | 75 | 68 | 63 | 83 | 74 | 67 | 62 | 72 | 66 | 62 | | 70 | 65 | 61 | | 69 | 64 | 60 | 59 |
| 6 | 80 | 69 | 62 | 57 | 78 | 68 | 62 | 57 | 67 | 61 | 56 | | 65 | 60 | 56 | | 64 | 59 | 55 | 54 |
| 7 | 75 | 64 | 57 | 52 | 74 | 64 | 57 | 52 | 62 | 56 | 52 | | 61 | 55 | 51 | | 60 | 55 | 51 | 49 |
| 8 | 71 | 60 | 53 | 48 | 70 | 59 | 53 | 48 | 58 | 52 | 48 | | 57 | 51 | 47 | | 56 | 51 | 47 | 46 |
| 9 | 67 | 56 | 49 | 44 | 66 | 56 | 49 | 44 | 54 | 48 | 44 | | 54 | 48 | 44 | | 53 | 48 | 44 | 42 |
| 10 | 64 | 53 | 46 | 41 | 63 | 52 | 46 | 41 | 51 | 45 | 41 | | 50 | 45 | 41 | | 50 | 45 | 41 | 39 |

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P246739

CATALOG NUMBER: LD8B15D010 ER8B15927 8LBM0MW

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 94.6 | 7.9 |
| 10°-20° | 227.1 | 18.9 |
| 20°-30° | 301.0 | 25.1 |
| 30°-40° | 246.8 | 20.6 |
| 40°-50° | 131.5 | 11.0 |
| 50°-60° | 92.5 | 7.7 |
| 60°-70° | 63.8 | 5.3 |
| 70°-80° | 33.2 | 2.8 |
| 80°-90° | 9.8 | 0.8 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 622.7 | 51.9 |
| 0°-40° | 869.5 | 72.4 |
| 0°-60° | 1093.5 | 91.1 |
| 0°-90° | 1200.3 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1200.3 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1065 | |
| 5° | 1034 | 95 |
| 15° | 805 | 227 |
| 25° | 663 | 301 |
| 35° | 397 | 247 |
| 45° | 162 | 131 |
| 55° | 102 | 93 |
| 65° | 64 | 64 |
| 75° | 32 | 33 |
| 85° | 9 | 10 |
| 90° | 0 | |



TEST NUMBER: P246739

CATALOG NUMBER: LD8B15D010 ER8B15927 8LBM0MW

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 1064.8 |
| 1° | 1067.9 |
| 2° | 1066.6 |
| 3° | 1060.2 |
| 4° | 1049.4 |
| 5° | 1033.9 |
| 6° | 1014.4 |
| 7° | 991.1 |
| 8° | 966.2 |
| 9° | 939.5 |
| 10° | 913.7 |
| 11° | 889.1 |
| 12° | 864.1 |
| 13° | 843.2 |
| 14° | 823.4 |
| 15° | 805.4 |
| 16° | 788.3 |
| 17° | 772.6 |
| 18° | 758.1 |
| 19° | 743.5 |
| 20° | 729.7 |
| 21° | 716.1 |
| 22° | 704.2 |
| 23° | 692.1 |
| 24° | 677.9 |
| 25° | 663.0 |
| 26° | 646.0 |
| 27° | 626.8 |
| 28° | 605.2 |
| 29° | 581.3 |
| 30° | 553.8 |
| 31° | 525.0 |
| 32° | 494.9 |
| 33° | 462.6 |
| 34° | 430.2 |
| 35° | 397.0 |
| 37.5° | 318.0 |
| 40° | 249.3 |
| 42.5° | 196.9 |
| 45° | 162.2 |
| 47.5° | 139.3 |
| 50° | 125.1 |
| 52.5° | 112.6 |
| 55° | 101.7 |
| 57.5° | 95.2 |



TEST NUMBER: P246739

CATALOG NUMBER: LD8B15D010 ER8B15927 8LBM0MW

CANDELA DISTRIBUTION (continued):

| | 0° |
|-------|------|
| 60° | 84.0 |
| 62.5° | 73.2 |
| 65° | 63.9 |
| 67.5° | 55.6 |
| 70° | 46.6 |
| 72.5° | 38.8 |
| 75° | 31.6 |
| 77.5° | 23.0 |
| 80° | 18.7 |
| 82.5° | 13.5 |
| 85° | 9.0 |
| 87.5° | 4.2 |
| 90° | 0.0 |

(END OF REPORT)