

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244873

Luminaire Tested: **LD8B15D010 ER8B15930 8LBM0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P244873  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201704)  
Test Lab: INNOVATION CENTER-P1  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B15D010 ER8B15930 8LBM0WMH  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT  
97 CRI 3000 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1206.2 lumens  
Efficiency: N/A  
Efficacy: 83.8 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.83  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P244873

CATALOG NUMBER: LD8B15D010 ER8B15930 8LBM0WMH

### Luminous Intensity Polar Plot






TEST NUMBER: P244873

CATALOG NUMBER: LD8B15D010 ER8B15930 8LBM0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94
2	108	104	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	86	83	82
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74	81	77	73	79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63
8	80	71	65	61	79	71	65	61	69	64	61	68	64	61	67	63	60	59
9	77	67	61	58	76	67	61	57	66	61	57	65	60	57	64	60	57	56
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	52

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P244873

CATALOG NUMBER: LD8B15D010 ER8B15930 8LBM0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	143.8	11.9
10°-20°	350.0	29.0
20°-30°	388.4	32.2
30°-40°	246.1	20.4
40°-50°	68.3	5.7
50°-60°	7.8	0.6
60°-70°	1.5	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	882.3	73.1
0°-40°	1128.4	93.5
0°-60°	1204.5	99.9
0°-90°	1206.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1206.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1514	
5°	1537	144
15°	1255	350
25°	862	388
35°	392	246
45°	76	68
55°	6	8
65°	2	2
75°	0	0
85°	0	0
90°	0	0
95°	0	0
105°	0	0
115°	0	0
125°	0	0
135°	0	0
145°	0	0
155°	0	0
165°	0	0
175°	0	0
180°	0	0



TEST NUMBER: P244873

CATALOG NUMBER: LD8B15D010 ER8B15930 8LBM0WMH

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1514.1
2.5°	1525.3
5°	1537.3
7.5°	1513.5
10°	1449.0
12.5°	1357.2
15°	1255.0
17.5°	1154.5
20°	1058.0
22.5°	963.3
25°	862.2
27.5°	744.0
30°	619.1
32.5°	498.2
35°	392.1
37.5°	296.3
40°	205.4
42.5°	127.7
45°	76.1
47.5°	43.8
50°	24.0
52.5°	11.8
55°	5.9
57.5°	4.5
60°	2.9
62.5°	1.6
65°	2.1
67.5°	1.1
70°	0.0
72.5°	0.3
75°	0.0
77.5°	0.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P244873

CATALOG NUMBER: LD8B15D010 ER8B15930 8LBM0WMH

**CANDELA DISTRIBUTION (continued):**

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)