

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P245665

Luminaire Tested: **LD8B15D010 ER8B15930 8LBN0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P245665
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P201794)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B15D010 ER8B15930 8LBN0GPH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: 2183 (1 lamp)
Luminaire Lumens: 1049.2 lumens
Efficiency: 48.1%
Efficacy: 72.9 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P245665

CATALOG NUMBER: LD8B15D010 ER8B15930 8LBN0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P245665

CATALOG NUMBER: LD8B15D010 ER8B15930 8LBN0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	57	57	57	57	56	56	56	56	53	53	53	51	51	51	49	49	49	48
1	55	54	52	51	54	52	51	51	51	50	49	49	48	48	47	47	46	45
2	52	50	48	47	51	49	48	46	48	46	45	46	45	44	45	44	43	43
3	50	47	45	43	49	46	44	43	45	43	42	44	43	41	43	42	41	40
4	48	44	42	40	47	44	42	40	43	41	39	42	40	39	41	40	38	38
5	45	42	39	37	45	41	39	37	41	38	37	40	38	36	39	37	36	36
6	43	39	37	35	43	39	37	35	38	36	35	38	36	34	37	35	34	33
7	41	37	35	33	41	37	35	33	36	34	33	36	34	32	35	34	32	32
8	40	35	33	31	39	35	33	31	35	32	31	34	32	31	34	32	31	30
9	38	34	31	29	37	33	31	29	33	31	29	33	31	29	32	30	29	28
10	36	32	29	28	36	32	29	28	31	29	28	31	29	28	31	29	27	27

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P245665

CATALOG NUMBER: LD8B15D010 ER8B15930 8LBN0GPH

ZONAL LUMENS:

CANDELA DISTRIBUTION:

Zone	Lumens	% Fixture	% Lamp	0°	Flux	
0°-10°	150.3	14.3	6.9	0°	1675	
10°-20°	327.5	31.2	15.0	5°	1642	150
20°-30°	350.8	33.4	16.1	15°	1167	328
30°-40°	190.1	18.1	8.7	25°	778	351
40°-50°	29.6	2.8	1.4	35°	298	190
50°-60°	0.7	0.1	0.0	45°	27	30
60°-70°	0.1	0.0	0.0	55°	0	1
70°-80°	0.0	0.0	0.0	65°	0	0
80°-90°	0.0	0.0	0.0	75°	0	0
90°-100°	0.0	0.0	0.0	85°	0	0
100°-110°	0.0	0.0	0.0	90°	0	0
110°-120°	0.0	0.0	0.0	95°	0	0
120°-130°	0.0	0.0	0.0	105°	0	0
130°-140°	0.0	0.0	0.0	115°	0	0
140°-150°	0.0	0.0	0.0	125°	0	0
150°-160°	0.0	0.0	0.0	135°	0	0
160°-170°	0.0	0.0	0.0	145°	0	0
170°-180°	0.0	0.0	0.0	155°	0	0
0°-30°	828.6	79.0	38.0	165°	0	0
0°-40°	1018.7	97.1	46.7	175°	0	0
0°-60°	1049.1	100.0	48.1	180°	0	0
0°-90°	1049.2	100.0	48.1			
90°-120°	0.0	0.0	0.0			
90°-150°	0.0	0.0	0.0			
90°-180°	0.0	0.0	0.0			
0°-180°	1049.2	100.0	48.1			



TEST NUMBER: P245665

CATALOG NUMBER: LD8B15D010 ER8B15930 8LBN0GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	1675.2
2.5°	1673.9
5°	1642.2
7.5°	1563.8
10°	1442.4
12.5°	1300.2
15°	1167.3
17.5°	1054.4
20°	956.0
22.5°	867.7
25°	777.9
27.5°	676.1
30°	556.5
32.5°	424.4
35°	297.7
37.5°	190.7
40°	110.0
42.5°	58.6
45°	27.4
47.5°	14.9
50°	4.8
52.5°	0.4
55°	0.0
57.5°	0.4
60°	0.4
62.5°	0.0
65°	0.0
67.5°	0.4
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0
92.5°	0.0
95°	0.0
97.5°	0.0
100°	0.0
102.5°	0.0
105°	0.0
107.5°	0.0
110°	0.0



TEST NUMBER: P245665

CATALOG NUMBER: LD8B15D010 ER8B15930 8LBN0GPH

CANDELA DISTRIBUTION (continued):

	0°
112.5°	0.0
115°	0.0
117.5°	0.0
120°	0.0
122.5°	0.0
125°	0.0
127.5°	0.0
130°	0.0
132.5°	0.0
135°	0.0
137.5°	0.0
140°	0.0
142.5°	0.0
145°	0.0
147.5°	0.0
150°	0.0
152.5°	0.0
155°	0.0
157.5°	0.0
160°	0.0
162.5°	0.0
165°	0.0
167.5°	0.0
170°	0.0
172.5°	0.0
175°	0.0
177.5°	0.0
180°	0.0

(END OF REPORT)