

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P249863

Luminaire Tested: **LD8B100D010 ER8B1009730 8LBN0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P249863
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13959)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B100D010 ER8B1009730 8LBN0H
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7216.0 lumens
Efficiency: N/A
Efficacy: 67.9 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.81
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 106.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P249863

CATALOG NUMBER: LD8B100D010 ER8B1009730 8LBN0H

Luminous Intensity Polar Plot





TEST NUMBER: P249863

CATALOG NUMBER: LD8B100D010 ER8B1009730 8LBN0H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76
5	93	85	79	75	92	84	79	75	82	78	74	81	77	74	79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67
7	84	75	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63
8	81	71	65	62	79	71	65	61	70	65	61	69	64	61	68	64	61	59
9	77	68	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56
10	73	64	58	55	72	64	58	55	63	58	54	62	57	54	61	57	54	53

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P249863

CATALOG NUMBER: LD8B100D010 ER8B1009730 8LBN0H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	902.5	12.5
10°-20°	2118.8	29.4
20°-30°	2315.8	32.1
30°-40°	1378.1	19.1
40°-50°	378.0	5.2
50°-60°	85.6	1.2
60°-70°	26.5	0.4
70°-80°	8.0	0.1
80°-90°	2.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	5337.1	74.0
0°-40°	6715.2	93.1
0°-60°	7178.9	99.5
0°-90°	7216.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7216.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9897	
5°	9738	903
15°	7604	2119
25°	5116	2316
35°	2181	1378
45°	442	378
55°	86	86
65°	27	26
75°	7	8
85°	2	3
90°	0	



TEST NUMBER: P249863

CATALOG NUMBER: LD8B100D010 ER8B1009730 8LBN0H

CANDELA DISTRIBUTION (FULL):

0°	
0°	9897.2
1°	9916.7
2°	9904.5
3°	9880.1
4°	9824.0
5°	9738.5
6°	9628.6
7°	9482.1
8°	9311.1
9°	9113.3
10°	8891.1
11°	8654.3
12°	8400.3
13°	8139.0
14°	7868.0
15°	7604.2
16°	7345.4
17°	7091.4
18°	6837.5
19°	6583.5
20°	6336.9
22.5°	5716.6
25°	5115.9
27.5°	4454.1
30°	3719.1
32.5°	2930.3
35°	2180.7
37.5°	1516.4
40°	1006.1
42.5°	659.3
45°	442.0
47.5°	293.0
50°	195.4
52.5°	119.7
55°	85.5
57.5°	61.0
60°	46.4
62.5°	34.2
65°	26.9
67.5°	17.1
70°	12.2
72.5°	9.8
75°	7.3
77.5°	4.9
80°	4.9



TEST NUMBER: P249863

CATALOG NUMBER: LD8B100D010 ER8B1009730 8LBN0H

CANDELA DISTRIBUTION (continued):

	0°
82.5°	2.4
85°	2.4
87.5°	2.4
90°	0.0

(END OF REPORT)