

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244495

Luminaire Tested: **LD8B15D010 ER8B15940 8LBS0H**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P244495
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-13)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B15D010 ER8B15940 8LBS0H
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
90 CRI 4000 CCT WITH SEMI-SPECULAR CLEAR TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1490.0 lumens
Efficiency: N/A
Efficacy: 103.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.23
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 14.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P244495

CATALOG NUMBER: LD8B15D010 ER8B15940 8LBS0H

Luminous Intensity Polar Plot





TEST NUMBER: P244495

CATALOG NUMBER: LD8B15D010 ER8B15940 8LBSOH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	102	103	100	98	99	97	95	95	94	93	91
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73
4	91	82	75	70	89	81	75	70	79	73	69	76	72	68	74	70	67	65
5	85	75	68	63	83	74	67	62	72	66	62	70	65	61	69	64	60	59
6	80	69	61	56	78	68	61	56	66	60	56	65	59	55	63	58	55	53
7	75	63	56	51	73	63	56	51	61	55	50	60	54	50	59	54	50	48
8	70	58	51	46	68	58	51	46	57	50	46	55	50	46	54	49	45	44
9	66	54	47	42	64	53	47	42	52	46	42	51	46	42	51	45	42	40
10	62	50	43	39	61	50	43	39	49	43	38	48	42	38	47	42	38	37

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	26664
5°	26574
10°	26374
15°	26187
20°	26009
25°	25668
30°	24875
35°	23471
40°	21331
45°	17553
50°	11701
55°	6097
60°	2874
65°	1510
70°	748
75°	524
80°	391
85°	318



TEST NUMBER: P244495

CATALOG NUMBER: LD8B15D010 ER8B15940 8LBSOH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.4	5.5
10°-20°	231.5	15.5
20°-30°	346.3	23.2
30°-40°	387.4	26.0
40°-50°	303.9	20.4
50°-60°	110.9	7.4
60°-70°	22.6	1.5
70°-80°	4.9	0.3
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	659.3	44.2
0°-40°	1046.7	70.2
0°-60°	1461.5	98.1
0°-90°	1490.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1490.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	865	
5°	858	81
15°	820	232
25°	754	346
35°	624	387
45°	402	304
55°	113	111
65°	21	23
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P244495

CATALOG NUMBER: LD8B15D010 ER8B15940 8LBS0H

CANDELA DISTRIBUTION (FULL):

	0°
0°	864.7
2.5°	863.4
5°	858.5
7.5°	851.5
10°	842.3
12.5°	831.7
15°	820.3
17.5°	807.6
20°	792.6
22.5°	775.1
25°	754.4
27.5°	728.9
30°	698.6
32.5°	663.0
35°	623.5
37.5°	579.1
40°	529.9
42.5°	471.4
45°	402.5
47.5°	324.7
50°	243.9
52.5°	170.9
55°	113.4
57.5°	72.5
60°	46.6
62.5°	30.8
65°	20.7
67.5°	13.2
70°	8.3
72.5°	5.7
75°	4.4
77.5°	3.1
80°	2.2
82.5°	1.3
85°	0.9
87.5°	0.4
90°	0.0

(END OF REPORT)