

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244933

Luminaire Tested: **LD8B15D010 ER8B15950 8LBS0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P244933  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-14)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B15D010 ER8B15950 8LBS0WMH  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
90 CRI 5000 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1514.0 lumens  
Efficiency: N/A  
Efficacy: 105.1 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 14.4  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P244933

CATALOG NUMBER: LD8B15D010 ER8B15950 8LBS0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P244933

CATALOG NUMBER: LD8B15D010 ER8B15950 8LBS0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	92	91
2	105	99	94	89	102	97	92	88	94	90	86	90	87	85	88	85	83	81
3	98	90	83	78	95	88	82	78	85	80	76	83	79	75	80	77	74	72
4	91	82	75	69	89	80	74	69	78	72	68	76	71	67	74	70	66	65
5	85	74	67	62	83	73	67	61	71	65	61	70	64	60	68	63	60	58
6	79	68	61	55	77	67	60	55	66	59	55	64	58	54	63	58	54	52
7	74	63	55	50	72	62	55	50	60	54	49	59	53	49	58	53	49	47
8	69	58	50	45	68	57	50	45	56	49	45	55	49	45	54	48	45	43
9	65	53	46	41	64	53	46	41	52	45	41	51	45	41	50	45	41	39
10	61	50	43	38	60	49	42	38	48	42	38	47	42	38	46	41	37	36

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	26470
5°	26388
10°	26152
15°	25894
20°	25612
25°	25208
30°	24519
35°	23400
40°	21685
45°	18311
50°	12564
55°	6930
60°	3485
65°	1963
70°	1064
75°	763
80°	479
85°	318



TEST NUMBER: P244933

CATALOG NUMBER: LD8B15D010 ER8B15950 8LBS0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	80.8	5.3
10°-20°	228.7	15.1
20°-30°	340.5	22.5
30°-40°	386.8	25.5
40°-50°	316.2	20.9
50°-60°	123.9	8.2
60°-70°	28.9	1.9
70°-80°	7.0	0.5
80°-90°	1.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	650.1	42.9
0°-40°	1036.9	68.5
0°-60°	1477.1	97.6
0°-90°	1514.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1514.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	858	
5°	852	81
15°	811	229
25°	741	341
35°	622	387
45°	420	316
55°	129	124
65°	27	29
75°	6	7
85°	1	1
90°	0	



TEST NUMBER: P244933

CATALOG NUMBER: LD8B15D010 ER8B15950 8LBS0WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	858.4
2.5°	857.0
5°	852.5
7.5°	844.8
10°	835.2
12.5°	823.3
15°	811.1
17.5°	796.5
20°	780.5
22.5°	761.9
25°	740.9
27.5°	716.3
30°	688.6
32.5°	657.1
35°	621.6
37.5°	582.4
40°	538.7
42.5°	485.9
45°	419.9
47.5°	342.5
50°	261.9
52.5°	188.1
55°	128.9
57.5°	84.2
60°	56.5
62.5°	38.7
65°	26.9
67.5°	17.8
70°	11.8
72.5°	8.2
75°	6.4
77.5°	4.6
80°	2.7
82.5°	1.4
85°	0.9
87.5°	0.5
90°	0.0

(END OF REPORT)