

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244291

Luminaire Tested: **LD8B15D010 ER8B159727 8LBW0H**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P244291  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P27940)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B15D010 ER8B159727 8LBW0H  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
97 CRI 2700 CCT WITH SEMI-SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1069.0 lumens  
Efficiency: N/A  
Efficacy: 74.2 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.12  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P244291

CATALOG NUMBER: LD8B15D010 ER8B159727 8LBW0H

### Luminous Intensity Polar Plot





TEST NUMBER: P244291

CATALOG NUMBER: LD8B15D010 ER8B159727 8LBW0H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  | 0   |     |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 | 100 |
| 1   | 113 | 109 | 107 | 104 | 110 | 107 | 105 | 102 | 103 | 101 | 99  |  | 99  | 98  | 96  |  | 96  | 95  | 93  | 92  |
| 2   | 106 | 100 | 95  | 91  | 103 | 98  | 94  | 90  | 95  | 91  | 88  |  | 92  | 89  | 86  |  | 89  | 87  | 85  | 83  |
| 3   | 99  | 92  | 86  | 81  | 97  | 90  | 85  | 81  | 88  | 83  | 79  |  | 85  | 81  | 78  |  | 83  | 79  | 77  | 75  |
| 4   | 93  | 84  | 78  | 73  | 91  | 83  | 77  | 72  | 81  | 75  | 71  |  | 79  | 74  | 71  |  | 77  | 73  | 70  | 68  |
| 5   | 87  | 77  | 71  | 66  | 85  | 76  | 70  | 65  | 75  | 69  | 65  |  | 73  | 68  | 64  |  | 71  | 67  | 63  | 62  |
| 6   | 82  | 71  | 65  | 60  | 80  | 71  | 64  | 59  | 69  | 63  | 59  |  | 68  | 62  | 58  |  | 66  | 62  | 58  | 56  |
| 7   | 77  | 66  | 59  | 54  | 75  | 65  | 59  | 54  | 64  | 58  | 54  |  | 63  | 57  | 53  |  | 62  | 57  | 53  | 52  |
| 8   | 72  | 61  | 54  | 50  | 71  | 61  | 54  | 50  | 60  | 54  | 49  |  | 58  | 53  | 49  |  | 57  | 53  | 49  | 47  |
| 9   | 68  | 57  | 50  | 46  | 67  | 57  | 50  | 46  | 56  | 50  | 46  |  | 55  | 49  | 45  |  | 54  | 49  | 45  | 44  |
| 10  | 64  | 53  | 47  | 42  | 63  | 53  | 47  | 42  | 52  | 46  | 42  |  | 51  | 46  | 42  |  | 50  | 45  | 42  | 40  |

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P244291

CATALOG NUMBER: LD8B15D010 ER8B159727 8LBW0H

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 67.5   | 6.3       |
| 10°-20°   | 193.8  | 18.1      |
| 20°-30°   | 291.7  | 27.3      |
| 30°-40°   | 288.8  | 27.0      |
| 40°-50°   | 146.7  | 13.7      |
| 50°-60°   | 59.1   | 5.5       |
| 60°-70°   | 17.9   | 1.7       |
| 70°-80°   | 3.1    | 0.3       |
| 80°-90°   | 0.4    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 553.0  | 51.7      |
| 0°-40°    | 841.8  | 78.7      |
| 0°-60°    | 1047.6 | 98.0      |
| 0°-90°    | 1069.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1069.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°  | Flux |
|-----|-----|------|
| 0°  | 717 |      |
| 5°  | 712 | 68   |
| 15° | 687 | 194  |
| 25° | 637 | 292  |
| 35° | 475 | 289  |
| 45° | 180 | 147  |
| 55° | 64  | 59   |
| 65° | 16  | 18   |
| 75° | 2   | 3    |
| 85° | 0   | 0    |
| 90° | 0   |      |



TEST NUMBER: P244291

CATALOG NUMBER: LD8B15D010 ER8B159727 8LBW0H

**CANDELA DISTRIBUTION (FULL):**

| 0°    |       |
|-------|-------|
| 0°    | 716.8 |
| 1°    | 715.3 |
| 2°    | 714.0 |
| 3°    | 713.7 |
| 4°    | 713.4 |
| 5°    | 712.5 |
| 6°    | 711.2 |
| 7°    | 708.8 |
| 8°    | 705.1 |
| 9°    | 701.7 |
| 10°   | 698.0 |
| 11°   | 694.9 |
| 12°   | 692.7 |
| 13°   | 691.2 |
| 14°   | 689.3 |
| 15°   | 687.1 |
| 16°   | 684.4 |
| 17°   | 681.0 |
| 18°   | 677.0 |
| 19°   | 672.3 |
| 20°   | 667.1 |
| 21°   | 661.5 |
| 22°   | 655.9 |
| 23°   | 650.1 |
| 24°   | 643.9 |
| 25°   | 637.1 |
| 26°   | 629.7 |
| 27°   | 620.1 |
| 28°   | 609.0 |
| 29°   | 595.7 |
| 30°   | 580.2 |
| 32.5° | 535.1 |
| 35°   | 475.2 |
| 37.5° | 400.4 |
| 40°   | 317.0 |
| 42.5° | 239.5 |
| 45°   | 179.8 |
| 47.5° | 137.5 |
| 50°   | 107.8 |
| 52.5° | 83.7  |
| 55°   | 63.6  |
| 57.5° | 47.3  |
| 60°   | 35.5  |
| 62.5° | 25.3  |
| 65°   | 16.4  |



TEST NUMBER: P244291

CATALOG NUMBER: LD8B15D010 ER8B159727 8LBW0H

**CANDELA DISTRIBUTION (continued):**

|       | 0°   |
|-------|------|
| 67.5° | 10.2 |
| 70°   | 6.5  |
| 72.5° | 4.0  |
| 75°   | 2.5  |
| 77.5° | 1.5  |
| 80°   | 0.9  |
| 82.5° | 0.6  |
| 85°   | 0.3  |
| 87.5° | 0.0  |
| 90°   | 0.0  |

(END OF REPORT)