

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P244945

Luminaire Tested: **LD8B15D010 ER8B159730 8LBS0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P244945  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-14)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B15D010 ER8B159730 8LBS0WMH  
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
97 CRI 3000 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1210.0 lumens  
Efficiency: N/A  
Efficacy: 84.0 lumens/watt  
Spacing Criteria (0/90/45): 1.19 / 1.19 / 1.25  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 14.4  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P244945

CATALOG NUMBER: LD8B15D010 ER8B159730 8LBS0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P244945

CATALOG NUMBER: LD8B15D010 ER8B159730 8LBS0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98		99	97	95		95	94	92	91
2	105	99	94	89	102	97	92	88	94	90	86		90	87	85		88	85	83	81
3	98	90	83	78	95	88	82	78	85	80	76		83	79	75		80	77	74	72
4	91	82	75	69	89	80	74	69	78	72	68		76	71	67		74	70	66	65
5	85	74	67	62	83	73	67	61	71	65	61		70	64	60		68	63	60	58
6	79	68	61	55	77	67	60	55	66	59	55		64	58	54		63	58	54	52
7	74	63	55	50	72	62	55	50	60	54	49		59	53	49		58	53	49	47
8	69	58	50	45	68	57	50	45	56	49	45		55	49	45		54	48	45	43
9	65	53	46	41	64	53	46	41	52	45	41		51	45	41		50	45	41	39
10	61	50	43	38	60	49	42	38	48	42	38		47	42	38		46	41	37	36

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P244945

CATALOG NUMBER: LD8B15D010 ER8B159730 8LBS0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	64.6	5.3
10°-20°	182.8	15.1
20°-30°	272.2	22.5
30°-40°	309.2	25.6
40°-50°	252.7	20.9
50°-60°	99.0	8.2
60°-70°	23.1	1.9
70°-80°	5.6	0.5
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	519.6	42.9
0°-40°	828.7	68.5
0°-60°	1180.5	97.6
0°-90°	1210.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1210.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	686	
5°	681	65
15°	648	183
25°	592	272
35°	497	309
45°	336	253
55°	103	99
65°	22	23
75°	5	6
85°	1	1
90°	0	



TEST NUMBER: P244945

CATALOG NUMBER: LD8B15D010 ER8B159730 8LBS0WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	686.1
2.5°	685.0
5°	681.3
7.5°	675.1
10°	667.5
12.5°	658.0
15°	648.2
17.5°	636.6
20°	623.8
22.5°	608.9
25°	592.2
27.5°	572.5
30°	550.3
32.5°	525.2
35°	496.8
37.5°	465.5
40°	430.6
42.5°	388.3
45°	335.6
47.5°	273.7
50°	209.3
52.5°	150.3
55°	103.0
57.5°	67.3
60°	45.1
62.5°	30.9
65°	21.5
67.5°	14.2
70°	9.5
72.5°	6.6
75°	5.1
77.5°	3.6
80°	2.2
82.5°	1.1
85°	0.7
87.5°	0.4
90°	0.0

(END OF REPORT)