

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P246993

Luminaire Tested: **LD8B120D010 ER8B120927 8LBMOLI**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P246993  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-81)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B120D010 ER8B120927 8LBM0LI  
Description: PORTFOLIO 8 INCH MEDIUM DISTRIBUTION 55 DEG CUTOFF RECESSED  
DOWNLIGHT  
97 CRI 2700 CCT WITH SPECULAR CLEAR TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9925.9 lumens  
Efficiency: N/A  
Efficacy: 83.9 lumens/watt  
Spacing Criteria (0/90/45): 0.67 / 0.67 / 0.75  
Luminous Opening: Point Source (0' x 0' x 0')  
CIE Type: Direct


Input Watts (W): 118.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P246993

CATALOG NUMBER: LD8B120D010 ER8B120927 8LBM0LI

### Luminous Intensity Polar Plot





TEST NUMBER: P246993

CATALOG NUMBER: LD8B120D010 ER8B120927 8LBM0LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	109	104	100	97	107	102	99	96	99	96	94		96	94	92		94	92	90	88
3	104	98	93	89	102	96	92	89	94	90	87		91	88	86		89	87	85	83
4	99	92	87	83	97	91	86	82	89	85	81		87	83	80		85	82	79	78
5	94	87	81	77	93	86	81	77	84	79	76		82	78	75		81	77	75	73
6	90	82	76	72	89	81	76	72	79	75	71		78	74	71		77	73	70	69
7	86	77	72	68	85	77	71	68	75	71	67		74	70	67		73	69	67	65
8	82	73	68	64	81	73	67	64	72	67	63		71	66	63		70	66	63	62
9	79	70	64	60	78	69	64	60	68	63	60		67	63	60		67	63	60	58
10	75	66	61	57	74	66	61	57	65	60	57		64	60	57		64	60	57	55

**AVERAGE LUMINANCE (cd/sqm):**





TEST NUMBER: P246993

CATALOG NUMBER: LD8B120D010 ER8B120927 8LBM0LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1419.6	14.3
10°-20°	3112.1	31.4
20°-30°	3173.9	32.0
30°-40°	1777.6	17.9
40°-50°	379.1	3.8
50°-60°	47.0	0.5
60°-70°	12.2	0.1
70°-80°	2.9	0.0
80°-90°	1.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7705.6	77.6
0°-40°	9483.2	95.5
0°-60°	9909.2	99.8
0°-90°	9925.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9925.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	16289	
5°	15550	###
15°	11205	3112
25°	6996	3174
35°	2818	1778
45°	421	379
55°	36	47
65°	14	12
75°	5	3
85°	5	2
90°	0	



TEST NUMBER: P246993

CATALOG NUMBER: LD8B120D010 ER8B120927 8LBM0LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	16288.6
2.5°	16105.2
5°	15550.2
7.5°	14657.1
10°	13555.0
12.5°	12372.3
15°	11204.6
17.5°	10029.8
20°	8949.8
22.5°	7944.8
25°	6996.2
27.5°	6000.4
30°	4949.1
32.5°	3850.6
35°	2817.9
37.5°	1887.9
40°	1173.5
42.5°	701.6
45°	421.2
47.5°	234.2
50°	137.4
52.5°	72.7
55°	35.8
57.5°	25.4
60°	21.9
62.5°	10.4
65°	13.8
67.5°	13.8
70°	1.1
72.5°	3.5
75°	4.6
77.5°	2.4
80°	0.0
82.5°	1.1
85°	4.6
87.5°	0.0
90°	0.0

(END OF REPORT)