

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P247985

Luminaire Tested: **LD8B150D010 ER8B150830 8LBW0WMH**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P247985  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-71)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LD8B150D010 ER8B150830 8LBW0WMH  
Description: PORTFOLIO 8 INCH WIDE DISTRIBUTION 60 DEGREE CUTOFF RECESSED  
DOWNLIGHT  
80 CRI 3000 CCT WITH WARM HAZE TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 15239.0 lumens  
Efficiency: N/A  
Efficacy: 96.1 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 158.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P247985

CATALOG NUMBER: LD8B150D010 ER8B150830 8LBW0WMH

### Luminous Intensity Polar Plot





TEST NUMBER: P247985

CATALOG NUMBER: LD8B150D010 ER8B150830 8LBW0WMH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	86	84	82
3	99	91	85	81	97	90	84	80	87	82	79	85	81	77	82	79	76	74
4	93	84	77	72	91	82	76	72	80	75	71	78	74	70	76	72	69	67
5	87	77	70	65	85	76	70	65	74	68	64	72	67	64	71	66	63	61
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56
7	77	66	59	54	75	65	58	54	64	58	53	62	57	53	61	56	53	51
8	72	61	54	49	71	61	54	49	59	53	49	58	53	49	57	52	49	47
9	68	57	50	46	67	56	50	46	55	49	45	54	49	45	54	49	45	43
10	64	53	47	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	331592
5°	329345
10°	324965
15°	320971
20°	317813
25°	311164
30°	281500
35°	226437
40°	163785
45°	110671
50°	80551
55°	58939
60°	43707
65°	29120
70°	12920
75°	5838
80°	4102
85°	4776



TEST NUMBER: P247985

CATALOG NUMBER: LD8B150D010 ER8B150830 8LBW0WMH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1007.6	6.6
10°-20°	2837.7	18.6
20°-30°	4144.1	27.2
30°-40°	3727.0	24.5
40°-50°	2038.3	13.4
50°-60°	1010.5	6.6
60°-70°	399.0	2.6
70°-80°	64.3	0.4
80°-90°	10.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	7989.4	52.4
0°-40°	11716.4	76.9
0°-60°	14765.2	96.9
0°-90°	15239.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	15239.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	10753	
5°	10640	###
15°	10054	2838
25°	9145	4144
35°	6015	3727
45°	2538	2038
55°	1096	1011
65°	399	399
75°	49	64
85°	14	10
90°	0	



TEST NUMBER: P247985

CATALOG NUMBER: LD8B150D010 ER8B150830 8LBW0WMH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	10753.3
2.5°	10723.5
5°	10639.8
7.5°	10531.2
10°	10378.3
12.5°	10215.7
15°	10054.2
17.5°	9881.1
20°	9684.9
22.5°	9460.8
25°	9145.4
27.5°	8614.6
30°	7905.8
32.5°	7012.4
35°	6015.2
37.5°	5019.9
40°	4068.8
42.5°	3212.0
45°	2537.8
47.5°	2033.9
50°	1679.1
52.5°	1366.5
55°	1096.3
57.5°	885.7
60°	708.7
62.5°	560.6
65°	399.1
67.5°	237.5
70°	143.3
72.5°	80.8
75°	49.0
77.5°	31.7
80°	23.1
82.5°	7.7
85°	13.5
87.5°	5.8
90°	0.0

(END OF REPORT)