

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250361

Luminaire Tested: **LD8B120D010 ER8B120927 8LBN0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250361
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13948)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B120D010 ER8B120927 8LBN0GPH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 2700 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7828.8 lumens
Efficiency: N/A
Efficacy: 66.2 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 118.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250361

CATALOG NUMBER: LD8B120D010 ER8B120927 8LBN0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P250361

CATALOG NUMBER: LD8B120D010 ER8B120927 8LBN0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88	92	89	86	89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72	79	75	71	77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66
8	83	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61	68	63	60	67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P250361

CATALOG NUMBER: LD8B120D010 ER8B120927 8LBNOGPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1123.0	14.3
10°-20°	2440.8	31.2
20°-30°	2620.4	33.5
30°-40°	1416.3	18.1
40°-50°	221.0	2.8
50°-60°	6.0	0.1
60°-70°	1.5	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6184.1	79.0
0°-40°	7600.4	97.1
0°-60°	7827.4	100.0
0°-90°	7828.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7828.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	12510	
5°	12263	###
15°	8715	2441
25°	5808	2620
35°	2225	1416
45°	204	221
55°	0	6
65°	0	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P250361

CATALOG NUMBER: LD8B120D010 ER8B120927 8LBNOGPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	12509.8
1°	12533.5
2°	12521.7
3°	12478.8
4°	12396.5
5°	12263.1
6°	12079.4
7°	11832.2
8°	11522.8
9°	11166.9
10°	10770.9
11°	10355.6
12°	9924.8
13°	9494.3
14°	9094.5
15°	8714.7
16°	8366.1
17°	8029.1
18°	7715.8
19°	7422.4
20°	7140.2
21°	6865.9
22°	6607.2
23°	6349.2
24°	6078.8
25°	5808.4
26°	5534.1
27°	5221.0
28°	4876.1
29°	4524.1
30°	4155.8
31°	3760.2
32°	3364.2
33°	2972.7
34°	2577.2
35°	2224.6
37.5°	1421.8
40°	822.6
42.5°	438.9
45°	203.8
47.5°	109.9
50°	35.6
52.5°	3.9
55°	0.0
57.5°	3.9



TEST NUMBER: P250361

CATALOG NUMBER: LD8B120D010 ER8B120927 8LBNOGPH

CANDELA DISTRIBUTION (continued):

	0°
60°	3.9
62.5°	0.0
65°	0.0
67.5°	3.9
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)