

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P250368

Luminaire Tested: **LD8B120D010 ER8B120930 8LBN0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P250368
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P13948)
Test Lab: INNOVATION CENTER-P1
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B120D010 ER8B120930 8LBN0GPH
Description: PORTFOLIO 8 INCH NARROW DISTRIBUTION 50 DEGREE CUTOFF RECESSED
DOWNLIGHT
97 CRI 3000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8254.0 lumens
Efficiency: N/A
Efficacy: 69.8 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.77
Luminous Opening: Point Source (0' x 0' x 0')
CIE Type: Direct


Input Watts (W): 118.3
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P250368

CATALOG NUMBER: LD8B120D010 ER8B120930 8LBN0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P250368

CATALOG NUMBER: LD8B120D010 ER8B120930 8LBNOGPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	107	112	109	107	105	105	104	102		101	100	99		98	97	96	94
2	109	104	101	97	107	103	99	96	99	97	94		96	94	92		94	92	90	89
3	104	98	93	90	102	97	92	89	94	90	88		92	89	86		89	87	85	83
4	99	92	87	83	97	91	86	83	89	85	82		87	84	81		85	82	80	78
5	95	87	82	78	93	86	81	77	84	80	77		83	79	76		81	78	75	74
6	90	82	77	73	89	81	76	72	80	75	72		79	75	71		77	74	71	70
7	86	78	72	68	85	77	72	68	76	71	68		75	71	67		74	70	67	66
8	83	74	68	64	81	73	68	64	72	67	64		71	67	64		70	66	63	62
9	79	70	65	61	78	70	64	61	69	64	61		68	63	60		67	63	60	59
10	76	67	61	58	75	66	61	58	65	61	57		65	60	57		64	60	57	56

AVERAGE LUMINANCE (cd/sqm):





TEST NUMBER: P250368

CATALOG NUMBER: LD8B120D010 ER8B120930 8LBNOGPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1184.0	14.3
10°-20°	2573.3	31.2
20°-30°	2762.6	33.5
30°-40°	1493.1	18.1
40°-50°	232.9	2.8
50°-60°	6.4	0.1
60°-70°	1.6	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6519.9	79.0
0°-40°	8013.0	97.1
0°-60°	8252.4	100.0
0°-90°	8254.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8254.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	13189	
5°	12929	###
15°	9188	2573
25°	6124	2763
35°	2345	1493
45°	215	233
55°	0	6
65°	0	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P250368

CATALOG NUMBER: LD8B120D010 ER8B120930 8LBNOGPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	13188.9
1°	13214.0
2°	13201.6
3°	13156.4
4°	13069.5
5°	12928.8
6°	12735.1
7°	12474.6
8°	12148.5
9°	11773.1
10°	11355.7
11°	10917.9
12°	10463.6
13°	10009.9
14°	9588.2
15°	9187.8
16°	8820.3
17°	8465.1
18°	8134.8
19°	7825.4
20°	7527.9
21°	7238.7
22°	6965.9
23°	6693.8
24°	6408.9
25°	6123.8
26°	5834.6
27°	5504.4
28°	5140.9
29°	4769.7
30°	4381.3
31°	3964.3
32°	3547.0
33°	3134.1
34°	2717.1
35°	2345.4
37.5°	1498.9
40°	867.2
42.5°	462.6
45°	214.9
47.5°	115.9
50°	37.4
52.5°	4.3
55°	0.0
57.5°	4.3



TEST NUMBER: P250368

CATALOG NUMBER: LD8B120D010 ER8B120930 8LBNOGPH

CANDELA DISTRIBUTION (continued):

	0°
60°	4.3
62.5°	0.0
65°	0.0
67.5°	4.3
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)