

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P249631

Luminaire Tested: **LD8B150D010 ER8B150840 8LBS0GPH**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P249631
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1801-521-95)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: PORTFOLIO
Catalog Number: LD8B150D010 ER8B150840 8LBS0GPH
Description: PORTFOLIO 8 INCH WIDE SHALLOW DISTRIBUTION 75 DEGREE CUTOFF RECESSED
DOWNLIGHT
80 CRI 4000 CCT WITH GRAPHITE TRIM
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 16049.0 lumens
Efficiency: N/A
Efficacy: 101.3 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.22
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 158.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P249631

CATALOG NUMBER: LD8B150D010 ER8B150840 8LBS0GPH

Luminous Intensity Polar Plot





TEST NUMBER: P249631

CATALOG NUMBER: LD8B150D010 ER8B150840 8LBS0GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91
2	105	99	94	90	102	97	92	89	94	90	87	91	87	85	88	85	83	81
3	98	90	84	79	96	88	83	78	85	81	77	83	79	75	81	77	74	72
4	91	82	75	69	89	80	74	69	78	73	68	76	71	67	74	70	66	65
5	85	75	67	62	83	73	67	62	72	66	61	70	64	60	68	63	60	58
6	79	68	61	56	78	67	60	55	66	59	55	64	59	54	63	58	54	52
7	74	63	55	50	73	62	55	50	61	54	50	59	54	49	58	53	49	47
8	69	58	51	45	68	57	50	45	56	50	45	55	49	45	54	49	45	43
9	65	54	46	42	64	53	46	41	52	46	41	51	45	41	50	45	41	39
10	61	50	43	38	60	49	43	38	48	42	38	47	42	38	47	41	38	36

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	284184
5°	283704
10°	282691
15°	280447
20°	276377
25°	269995
30°	260093
35°	245583
40°	223856
45°	182644
50°	132151
55°	83422
60°	44787
65°	20299
70°	6897
75°	3431
80°	2291
85°	1061



TEST NUMBER: P249631

CATALOG NUMBER: LD8B150D010 ER8B150840 8LBS0GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	870.6	5.4
10°-20°	2475.2	15.4
20°-30°	3645.0	22.7
30°-40°	4058.3	25.3
40°-50°	3205.2	20.0
50°-60°	1437.0	9.0
60°-70°	317.2	2.0
70°-80°	35.8	0.2
80°-90°	4.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	6990.7	43.6
0°-40°	11049.1	68.8
0°-60°	15691.3	97.8
0°-90°	16049.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	16049.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9216	
5°	9165	871
15°	8785	2475
25°	7935	3645
35°	6524	4058
45°	4188	3205
55°	1552	1437
65°	278	317
75°	29	36
85°	3	5
90°	0	



TEST NUMBER: P249631

CATALOG NUMBER: LD8B150D010 ER8B150840 8LBS0GPH

CANDELA DISTRIBUTION (FULL):

	0°
0°	9215.9
2.5°	9202.0
5°	9165.3
7.5°	9108.6
10°	9028.2
12.5°	8919.9
15°	8784.8
17.5°	8619.9
20°	8422.2
22.5°	8194.7
25°	7935.4
27.5°	7636.4
30°	7304.6
32.5°	6924.1
35°	6523.8
37.5°	6093.6
40°	5561.1
42.5°	4902.5
45°	4188.2
47.5°	3461.1
50°	2754.7
52.5°	2109.0
55°	1551.7
57.5°	1083.8
60°	726.2
62.5°	460.0
65°	278.2
67.5°	155.0
70°	76.5
72.5°	41.7
75°	28.8
77.5°	20.9
80°	12.9
82.5°	7.0
85°	3.0
87.5°	1.0
90°	0.0

(END OF REPORT)